



D

C

B

A



ACT 26 X X XX X X

KEYING POSITION

CONTACT CODE

P = 500 CYCLE PIN

S = 500 CYCLE SOCKET

A = LESS PIN

B = LESS SOCKET

H = 1500 CYCLE PIN

J = 1500 CYCLE SOCKET

INSERT ARRANGEMENT

SHELL SIZE

FINISH

J = OLIVE DRAB CADMIUM

M = NICKEL

STRAIGHT PLUG

GENERAL IDENTIFIER

ACT = ALL COMPOSITE TECHNOLOGY

5. FOUR FLATS FOR SHELL SIZES A - E.
EIGHT FLATS FOR SHELL SIZES F - J.
4. FOR APPLICABLE KEYING DIAGRAM, SEE MIL-DTL-38999.
FOR INSERT ARRANGEMENTS, SEE MIL-STD-1560. CONSULT
FACTORY FOR AVAILABILITY.
3. GENERAL SPECIFICATIONS: THIS CONNECTOR MEETS THE
INTERMATEABILITY REQUIREMENTS OF MIL-DTL-38999 SERIES III.
2. MATERIAL/FINISH
- SHELL - COMPOSITE, PLATED.
- COUPLING RING - COMPOSITE, UNPLATED.
- CONTACTS - COPPER ALLOY, DEUTSCHCOAT V (H/J) OR GOLD (P/S).
- RESILIENT INSERTS - SILICONE ELASTOMER.
- PLASTIC INSERTS - THERMOPLASTIC.

1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
THREAD CALLOUT IS METRIC.

PART NUMBER	SHELL SIZE	Ø A MAX.	B THREAD
ACT26xAxxxx	09	.858	M12x1.0-6g 0.100R
ACT26xBxxxx	11	.984	M15x1.0-6g 0.100R
ACT26xCxxxx	13	1.157	M18x1.0-6g 0.100R
ACT26xDxxxx	15	1.280	M22x1.0-6g 0.100R
ACT26xExxxx	17	1.406	M25x1.0-6g 0.100R
ACT26xFxxxx	19	1.516	M28x1.0-6g 0.100R
ACT26xGxxxx	21	1.642	M31x1.0-6g 0.100R
ACT26xHxxxx	23	1.768	M34x1.0-6g 0.100R
ACT26xJxxxx	25	1.890	M37x1.0-6g 0.100R

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CRAIG BROWN CHK EHAB ALAWNEH APVD -	150102 150102		TE Connectivity		
DIMENSIONS: INCH		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.005 4 PLC ±0.0001 ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		NAME ACT SERIES PLUG ENVELOPE -	
MATERIAL -		-		SCALE 3.000		SHEET 1 OF 1	
-		-		CUSTOMER DRAWING		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[YACT26MJ04JC000000](#)