

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION —, —, —
© COPYRIGHT — TE Connectivity Ltd.	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	24OCT2019	RV	MB

General Specifications

Temperature Rating —  
-70°C TO + 125°C

Altitude — 300,000 Feet

Shock\* —  
Z & Y Enclosures —  
200 g for 6 mS

W, X & M Enclosures —  
100 g for 6 mS

Vibration, Sinusoidal\* —  
Z & Y Enclosures —  
0.12 DA 10 to 70Hz  
30 g 70 to 3000Hz  
W, X & M Enclosures —  
0.12 DA 10 to 57Hz  
20 g 57 to 3000Hz

Vibration, Random\* —  
Z & Y Enclosures —  
0.4 g<sup>2</sup>/Hz 50-2000Hz  
W, X & M Enclosures —  
0.2 g<sup>2</sup>/Hz 50-2000Hz

Dielectric Strength —  
At Sea Level —  
All circuits to ground and circuit to  
circuit — 1250 V rms  
Coil to ground — 1000 V rms  
At 80,000 Feet — 350 V rms

Insulation Resistance —  
Initial (500 VDC) — 100 MΩ Min.  
After Life or Environmental Tests —  
50 MΩ Min.

Operate Time at Nominal  
Voltage —  
DC Relays — 15 ms or less  
AC Relays — 20 ms or less

Release Time at Nominal  
Voltage —  
DC Relays — 15 ms or less  
AC Relays — 50 ms or less

\* Max. contact opening under vibration  
or shock 10 microseconds

Contact Rating — Amperes  
Ratings Are Continuous Duty

Type of Load	Life (Min.) Cycles x 10 <sup>3</sup>	28 VDC	120VAC 400Hz	120/200VAC	
				400Hz-3Ø	60Hz-3Ø*
Resistive	100	10	10	10	2.5
Inductive	20	8	8	8	2.5
Motor	100	4	4	4	2.0
Lamp	100	2	2	2	1.0

\*60 Hz loads rated for 10,000 operations

Overload Current — 40 AMPS DC, 60 AMPS 400Hz  
Rupture Current — 50 AMPS DC, 80 AMPS 400Hz  
Contact Make Bounce —1 MILLISECOND AT NOMINAL VOLTAGE  
Max. Contact Drop at 10 Amps — INITIAL 0.100 VOLTS  
End of Life — 0.125 VOLTS

Coil Data

Coil Code	Nominal Voltages	Freq. Hz	DC Res. AC Amps (B)	Over Temperature Range		
				Pickup or Below Volts	Dropout or Above Volts	Must Hold Voltage (C)
1	6	DC	18 Ω	4.5	0.3	2.5
2	12	DC	70 Ω	9.0	0.75	4.5
3	28	DC	290 Ω	18.0	1.5	7.0
4 (A)	28	DC	290 Ω	18.0	1.5	7.0
5	48	DC	865 Ω	32.0	2.5	14.0
6	28	400Hz	225 mA	22.0	1.25	10.0
7	28	50/400Hz	120 mA	22.0	1.25	10.0
8	115	400 Hz	40 mA	90.0	5.0	40.0
9	115	50/400 Hz	30 mA	95.0	5.0	40.0

- A. CODE 4 COILS HAVE BACK EMF SUPPRESSION TO 42 VOLTS MAX.  
B. DC COIL RESISTANCE ± 10% AT 25°C; AC COIL MAX. CURRENT AT NOMINAL VOLTAGE.  
C. RELAY WILL STAY IN PICKED-UP STATE DOWN TO MUST HOLD VOLTAGES SHOWN.  
D. MAX. OVER-VOLTAGE: 6 & 12 VDC COILS 120% OF NOMINAL; ALL OTHERS 110% OF NOMINAL.  
E. COILS AVAILABLE FOR OTHER VOLTAGES AND FOR AC 50/60HZ.

NOTE: Only DC Coil Models are QPL Approved.

The Series FCA-410 relay is a polarized single-side stable design, where the flux from a permanent magnet provides the armature holding force in the deactivated state, and its flux path is switched and combined with the coil flux in the operated state. This results in appreciably increased contact pressure in both states over that of a spring return nonpolar

design. We also manufacture 2-pole and 6-pole versions of this relay.

FCA-210 — 10 Amp DPDT Relay

FCA-412 — 12 Amp 4PDT Relay



Available

FCA-415 — 15 Amp 4PDT, Has the same specifications as the FCA-410 except is rated at 15 amps. (Commercial Only)



Product Facts

- Hermetically Sealed
- All Welded Construction
- Balanced Force
- Permanent Magnet Drive
- 4PDT switching in one inch cube
- Contacts — Silver Cadmium Oxide with Gold Plating
- Coils for DC and AC 50 to 400Hz or 400Hz
- Weight 2.72 ounces max. (77 grams max.)
- Qualified to M83536/15, /16

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RV	24OCT2019	<div> TE Connectivity</div>			
		CHK RV	24OCT2019				
DIMENSIONS: INCHES	<div>TOLERANCES UNLESS OTHERWISE SPECIFIED:</div> <div>0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —</div>	APVD MB	24OCT2019	NAME  FCA-410-SERIES  —  —			
		PRODUCT SPEC  —					
		APPLICATION SPEC  —					
		WEIGHT —					
MATERIAL  —		FINISH  —	CUSTOMER DRAWING		SIZE A3	CAGE CODE —	DRAWING NO C-FCA-410-SERIES
				SCALE NTS	SHEET 1 of 2	REV A	





# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M83536/16-024L](#)