






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED FOR PRODUCTION	06UG2019	RK	PS

NOTES:

1. MATERIAL AND FINISH:
HOUSING : POLYAMIDE 66, UL94V-0, COLOR GREEN.
TERMINAL : COPPER ALLOY, TIN PLATED.
2. MECHANICAL
MIN. PC BOARD HOLES DIAMETER : 1.5 mm
3. ELECTRICAL
RATED VOLTAGE : 300 V
RATED CURRENT : 16 A
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE: -40°C TO +105°C
- 5 NOT CUMULATIVE TOLERANCE.

81.6	16	1-2351885-6
76.6	15	1-2351885-5
71.6	14	1-2351885-4
66.6	13	1-2351885-3
61.6	12	1-2351885-2
56.6	11	1-2351885-1
51.6	10	1-2351885-0
46.6	9	2351885-9
41.6	8	2351885-8
36.6	7	2351885-7
31.6	6	2351885-6
26.6	5	2351885-5
21.6	4	2351885-4
16.6	3	2351885-3
11.6	2	2351885-2
DIM A	NO. OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12APR2019 RAGHAVENDRA.K	TE Connectivity HEADER 180 DEG. 5.0mm PITCH TAIL LENGTH 4.5mm		
DIMENSIONS: mm		CHK 01JUL2019 KARTHIK.JK			
		APVD 02JUL2019 PRASHANTH.S			
		PRODUCT SPEC			
		APPLICATION SPEC	NAME		
MATERIAL SEE NOTES		WEIGHT	SIZE	CAGE CODE	DRAWING NO
			A3	00779	C-2351885
		CUSTOMER DRAWING	SCALE	SHEET	REV
			3:1	1 OF 1	A



RECOMMENDED PC BOARD LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2351885-6](#)