



SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

DIMA DI FORATURA SU C.S.
(RECOMMENDED P.C.B. HOLE PATTERN)

10 OBSOLETE	2	6.2	3.96	1.6	280609-1	280614-1	280614-2	280614-4	280614-3
	12	45.9	43.59	21.4	280613-1	280613-2	280613-4	280613-3	
	10	37.9	35.66	17.5	280612-1	280612-2	280612-4	280612-3	
	8	30.0	27.74	13.5	280611-1	280611-2	280611-4	280611-3	
	6	22.1	19.81	9.5	280610-1	280610-2	280610-4	280610-3	
	4	14.2	11.89	5.6	280609-1	280609-2	280609-4	280609-3	
	2	6.2	3.96	1.6					
N° POS.	DIM. "A"	DIM. "B"	DIM. "C"	P.N. STAGNATO (TIN PLTD. VERSION)	DORATO 0.37µm AREA CONTATTO, STAGNATO NELLA ZONA A SALDARE (0.37µm GOLD PLTD ON CONTACT AREA, TIN PLTD ON SOLDER TAIL)	DORATO 0.76µm AREA CONTATTO, STAGNATO NELLA ZONA A SALDARE (0.76µm GOLD PLTD ON CONTACT AREA, TIN PLTD ON SOLDER TAIL)	DORATO 1.27µm AREA CONTATTO, STAGNATO NELLA ZONA A SALDARE (1.27µm GOLD PLTD ON CONTACT AREA, TIN PLTD ON SOLDER TAIL)		

CUSTOMER DRAWING FOR REFERENCE ONLY

DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED

RELEASE FOR PUBLICATION

19

TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS OTHERWISE SPECIFIED)

± 0.4

ANGOLI (ANGLES) ± 2°

DIS. (DR.) 27-06-1991 C.CORDOLA

DIAM. ISOLANTE (INS. DIA. RANGE)

RANGO FILO (WIRE RANGE)

SCALA (SCALE)

TE TE Connectivity

DESCRIZIONE (DESCRIPTION) AMP-MODU MODI STRAIGHT VERSION POST SUPPORT ASS'Y

S	STREAMLINING OF CONTACT BASE MATERIAL CHANGED TO BRASS	SMT	09APR 2013	CONT. (CHK.)	R.Cantore
R2	REVISED PER ECO-11-005140	HMR	24MAY11	APP. (APP.)	6-3-1991
REV. (REV.)	REVISIONI (REVISION RECORD)	DIS. (DR.)		LOC. (LOC.)	SIZE (SIZE)
				NUMERO (DWG NO)	REV. (REV.)
				I A3 C-280609	S
				FOGLIO (SHEET)	DI (OF)
				1	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[280609-1](#)