

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	22OCT2019	RV	MB

Specifications

Timing Data					
Timing Action					
Delay on Operate or Delay on Release					
Time Delay, Fixed – M83726/28, /29 and Commercial 28C, 29C					
Select from 0.1 to 600 sec for Commercial Models					
Select from 0.1 to 500 sec for Mil-Spec Models					
Time Delay, Adjustable – M83726/30, /31 and Commercial 30C, 31C					
Select one decade between 0.1 to 1.0 and 60 to 600 seconds					
Timing Accuracy (note 1)					
±10% of Nominal Value					
Recycle Time (note 2)					
50 ms, max., to next cycle.					
Power Interrupts					
Accuracy is not affected by power interruptions up to 1 ms spaced at least 10ms apart.					
Input Data					
Input Voltage					
28 Vdc nominal, range 20 - 32 Vdc					
Duty Rating					
Continuous					
Input Current					
110 mAdc Max @ 25°C					
Control Voltage (applies only to Delay on Release type)					
20 - 32 Vdc					
Control Current					
15 mAdc Max (applies only to delay on release types)					
Input Voltage Polarity Protection					
The timer will be inoperative during, and undamaged by, reversal of the polarity of the input voltage.					
Output Data					
Contact Form					
2 Form C (DPDT)					
Contact Material					
Silver Cadmium Oxide, Gold plated					
Contact Rating in Amps (Continuous Duty)					
Type of Load	Life (Min.) Cycles	28 Vdc	115 Vac 400Hz	115/200 Vac – 3 phase 400 Hz.	60 Hz.*
Resistive	100 x 10³	10	10	10	2.5
Inductive	20 x 10³	8	8	8	2.5
Motor	100 x 10³	4	4	4	2.0
Lamp	100 x 10³	2	2	2	1.0
* 60 Hz. loads are rated at 10 x 10³ cycles.					

Overload Current	40 Adc; 60A, 400 Hz.
Rupture Current	50 Adc; 80A, 400 Hz.
Max. Contact Drop at 10A	Initial 0.150V; After Life 0.175V

Electrical Data	
Electrostatic Discharge Withstand Voltage	16,000V
Transients (note 3):	
Positive Transients	+80V
Self-generated Transients	±50V, Max.
Spike Susceptibility	±600V, 10 µs, Max.
Insulation Resistance (note 4)	1,000 megohms at 500Vdc, between each pin and case
Dielectric Strength (note 4)	1,000Vrms at 60 Hz at sea level, between case and all pins connected together

Environmental Data	
Ambient Temperature Range, Operating	-55°C to +125°C
Altitude	80,000 feet maximum
Shock Resistance	100 G's, 6 ms.
Vibration Resistance, Sinusoidal	Z & Y Enclosure: 30 G's, 33-3000Hz.; X & W Enclosure: 20 G's, 33-3000Hz.
Mechanical Data	
Approximate Weight	2.5 oz. (71g) Max.

NOTES

1. The accuracy requirement applies to any combination of operating temperature and voltage. Add ±10ms for timing less than one second.
2. Recycle time to assure that the next timing cycle will be completed. Units can be recycled during timing and after time-out:
Delay on operate models – Power must be OFF the input at least 10 ms. Delay on release models – Power must be ON the control terminal at least 10 ms.
3. Transient specifications are based on a maximum duty cycle of 1/50.
4. All wired terminals must be connected together during this test. Dielectric withstanding voltage and insulation resistance are measured between all mutually insulated wired terminals and between all these terminals and case.
5. Inductive loads must be diode suppressed.

Product Facts

- Qualified to:
MIL-PRF-83726/28
MIL-PRF-83726/29
MIL-PRF-83726/30
MIL-PRF-83726/31
- Fixed delay on operate, fixed delay on release, adjustable delay on operate & adjustable delay on release
- Meets or exceeds electrostatic discharge MIL-STD-1686 Class Non-Sensitive
- Welded hermetically sealed enclosure occupies about 1 in³ (16.4 cm³)
- 10A, 2 form C (DPDT) output contacts

TD2 series time delay relays are available for delay on operate or delay on release operation. Either can be supplied as fixed or resistor adjustable types. Both military and commercial versions are offered.

These products consist of solid state timing circuits controlling our FCA-210 series relays, providing 2 Form C (DPDT) output contacts rated 10 amps. The internal timing circuit uses an R/C controlled oscillator with a program-

mable digital pulse counter, gating a semiconductor switch to operate the relay. Timing is independent of whether the controlling voltage is a ramp or step function.

For the adjustable models the user specifies a one decade range in seconds, within which the required delay will be set. This range is programmed internally at the time of manufacture. The required delay is obtained by calculating the oscillator timing resistor as

follows and connecting it externally to terminals 1D - 3D as below.

$R_{EXT} = [(T_1 / T_0) - 1] 100K \text{ Ohms}$

T₀ = Minimum time of selected decade in seconds.


T₁ = Required time delay.

EXAMPLE

Selected Range = 3-30 sec

Required Time = 15 sec


$R_{EXT} = [(15/3) - 1] 100K = 400K$




Timing Action and Terminal Wiring

Delay On Operate:


The time delay starts on the application of input voltage to X1-X2. The timing circuit energizes the end of the time delay period.



Fixed Model




Adjustable Model




Delay On Release:


The input voltage is continuous to X1-X2. When the control voltage is applied to C1-X2 the timing circuit and the relay are both energized. The time delay starts when the control voltage is shut off.





Fixed Model




Adjustable Model



Terminal designations shown in the diagrams above are for reference only. They do not appear on the relay header.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RV	22OCT2019	<div>TE Connectivity</div>					
		CHK RV	22OCT2019						
DIMENSIONS: INCHES	<div>TOLERANCES UNLESS OTHERWISE SPECIFIED:</div> <div>0 PLC ± -</div> <div>1 PLC ± -</div> <div>2 PLC ± -</div> <div>3 PLC ± -</div> <div>4 PLC ± -</div> <div>ANGLES ± -</div>	APVD MB	22OCT2019	NAME					
		PRODUCT SPEC	C-TD2-SERIES TIME DELAY RELAY						
		—	—						
		APPLICATION SPEC	—						
MATERIAL —		FINISH —	—	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	WEIGHT —		A3	—	C-TD2-SERIES		—		
CUSTOMER DRAWING				SCALE	NTS	SHEET	1 OF 2	REV	A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1617805-2](#)