
**3D VIEW**

6. SMALL NON-FILLS ARE ACCEPTABLE INSIDE OF PART, INCLUDING SUPPLIER MARKING.

5. SMALL MATERIAL EXTENSION IS ACCEPTABLE ON THIS END ALL AROUND. WALL THICKNESS ON THIS END MAY VARY.

4. BOTTOM OF PART MOLDED OPEN.

3. THIS ACCESSORY PART IS PROVIDED WITHOUT TYPICAL TRANSPORTATION INDUSTRY PROCESS CONTROLS. NO VALIDATION TESTING HAS BEEN PERFORMED. CUSTOMER IS RESPONSIBLE FOR DETERMINING PRODUCT PERFORMANCE AND SUITABILITY FOR APPLICATION.

2. TEMPERATURE RATING: -29°C TO +100°C [-20°F TO +212°F]

1. THIS PART IS USED ON
 DRB12-102PX(N)E-XXXX RECEPTACLE
 DRB16-102SXE-XXXX PLUG
 DRB12-128PX(N)E-XXXX RECEPTACLE
 DRB16-128SXE-XXXX PLUG
 WHERE X=A,B,C,D KEYS AND XXXX=MODIFICATION

NOTES:

TE INTEERNA PN	DEUTSCH PN
DRB102-BT	DRB102-BT

DIMENSIONS: MM[INCH]		DWN D.MEYER	28JUN2014	MATERIAL PVC		FINISH BLACK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK P.CARNAHAN	28JUN2014				
0 PLC ± 1 PLC ± 2 PLC ±0.63[.025] 3 PLC ± 4 PLC ± ANGLES ±5°		APVD D.MEYER	28JUN2014				
		PRODUCT SPEC		NAME BOOT, LARGE DRB SERIES			
		APPLICATION SPEC		SIZE A 4	CAGE CODE 4AFU8	DRAWING NO C-DRB102-BT	RESTRICTED TO
		WEIGHT 84.00 G					
		CUSTOMER DRAWING		SCALE 3:10	SHEET 1 OF 1	REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DRB102-BT](#)