





CAVITA' ADATTA PER CONTATTI:
(TYP. CAVITY FOR CONTACTS:)

282374-1 SEZ. 0.3-0.5 mm² (FIAT No. 1-23197-44)
282375-1 SEZ. 0.75-1.5 mm² (FIAT No. 1-24834-44)



OBSOLETE	282442-4	GRIGIO (GREY)	PBT (PBT UNFILLED)	282441-4
	282442-3	BLU (BLUE)		282441-3
	282442-2	NERO (BLACK)		282441-2
	282442-1	BIANCO (NATURAL)		282441-1
PORTAMASCHI VOLANTE (CAP HOUSING)		COLORE (COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED

RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE)

SCALA
(SCALE)

2:1

TE Connectivity

DESCRIZIONE
(DESCRIPTION) 070 SERIES MULTILOCK*
CONN. PLUG HOUSING 6 POSITION
(PORTAFEMMINE) DOUBLE ROW

LOC. SIZE NUMERO
(DWG NO)

I A3 C-282441

REV. FOGLIO
(SHEET)

B2 1 01 3

REV. (REV. LTR.)

REVISIONI
(REVISION RECORD)

DIS. DATA
(OR) (DATE)

APP. (APP.)

CONT. C. TARTARI
(CHK) 23 MAY '97

DIS. M. PALMA
(OR.) 23 MAY '97

AGG. CODICE FIAT

R.M. 25-10 93

AGGIORNATO

R.M. 1-4 93

REVISED PER ECO-20-003218

AP/VN 08MAY 2020

REVISI

M.G. 31-5 05

RELEASED AND REVISED FOR

M.P. 29-7 97

ET00-0298-97

1) PER RAPPRESENTAZIONE DIMA CONTROPARTE VEDERE FOGLIO 3 DI 3.
(FOR COUNTERPART DETAIL SEE SHEET 3 OF 3).


QUOTA VALIDA SOLO PER VERSIONE 282441-1.
(VALID DIMENSION ONLY FOR 282441-1 VERSION)

DISTRIBUZIONE
(PRINT DIST.)

SCALA NON IMPEGNATIVA (DO NOT SCALE)	
DIMENSIONI IN (DIMENSIONS IN)	mm




PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



P/N 282366-4 GRIGIO
(GREY)

—ASSE CAVITA'
(CAVITY AXIS)



3.1^{+0.1}_{-0.2}

[illegible]

COLORE (COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION		19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
(TOLERANCES, UNLESS OTHERWISE SPECIFIED)				SCALA (SCALE)	
± 0.3				2:1	
ANGOLI (ANGLES)		 TE Connectivity			
DIS. (DIM.)		DESCRIZIONE (DESCRIPTION) 070 SERIES MULTILOCK* CONN. PLUG HOUSING 6 POSITION (PORTAFEMMINE) DOUBLE ROW			
CONT. (CHK)		LOC. SIZE		REV.	
APP. (APP.)		NUMERO (DWG NO)		FOGLIO (SHEET)	
SEE SHEET 1 OF 3		I A3		B2	
		C-282441		2 DI (OF) 3	

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



Figure 1 shows three technical drawings of the rear view of a mechanical part, labeled 282441-2, 282441-3, and 282441-4. Each drawing includes dimensions and tolerances:

- 282441-2:** Dimensions include 12.20, 2.30, 1.80, 3.6 (+0.3/-0.15), 6.2 (+0.15/-0.15), 2.6 (+0/-0.15), 1.4 (+0.2/-0.2), and 1.80. The ASSE -X- (AXIS -X-) is indicated at the bottom.
- 282441-3:** Dimensions include 12.20, 2.30, 1.80, 3.6 (+0.3/-0.15), 2.6 (+0.15/-0.15), 1.0 (+0.15/-0.15), 1.4 (+0.2/-0.2), and 1.80. The ASSE -X- (AXIS -X-) is indicated at the bottom.
- 282441-4:** Dimensions include 12.20, 2.30, 1.80, 3.6 (+0.3/-0.15), 4.4 (+0.15/-0.15), 0.8 (+0/-0.15), 1.4 (+0.2/-0.2), and 1.80. The ASSE -X- (AXIS -X-) is indicated at the bottom.

AMP-ITA 7523 - 5/02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[282441-1](#)