





THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	20
© COPYRIGHT 20		ALL RIGHTS RESERVED.	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

- 1 MATERIALS AND FINISH
HOUSING : PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP : BRASS, NICKEL PLATED.
TERMINAL : BRASS, TIN PLATED.
CLAMPING SCREW : M3, BRASS, NICKEL PLATED.
2. MECHANICAL
WIRE STRIPPING LENGTH : 5.0 - 6.0 mm
MIN. PC BOARD HOLES DIAMETER : 1.1 mm
MAX. PC BOARD THICKNESS : 2.4 mm
RECOMMENDED TIGHTENING TORQUE FOR SCREW : 0.5 Nm.
3. ELECTRICAL
WIRE RANGE : 16-30 AWG.
MAX. VOLTAGE : 600 V
MAX CURRENT : 13.5 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE : -40°C TO +110°C
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE NO E60677.
- 6 NOT CUMULATIVE TOLERANCE.
- 7 INK MARKING COLOR WHITE, UNLESS OTHERWISE SPECIFIED.
NUMERICAL SEQUENCE : FROM LEFT TO RIGHT, UNLESS
OTHERWISE SPECIFIED.
8. PACKED IN TRAY.



282838-7 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI	24AUG2001	 TE Connectivity					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK D. BIEVENOUR	24AUG2001	NAME TERMINAL BLOCK PCB MOUNT SIDE ENTRY WIRE 10mm PITCH					
	0 PLC ± 1 PLC ±.3 2 PLC ±.25 3 PLC ± 4 PLC ± ANGLES ±2	APVD D. BIEVENOUR	24AUG2001						
MATERIAL	FINISH	PRODUCT SPEC	108-20166	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		APPLICATION SPEC	114-20079	A3	00779	C-282838	-		
		WEIGHT	-						
CUSTOMER DRAWING				SCALE	4:1	SHEET	2 OF 2	REV	E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-282838-0](#)