





LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	E	PACKAGING CHANGED FROM BLACK POLYURETHANE SPONGE TO TRAY	06MAR2018	RK	PS	





284093-3 AS SHOWN



8	125.0	25	2-284093-5
	120.0	24	2-284093-4
	115.0	23	2-284093-3
	110.0	22	2-284093-2
	105.0	21	2-284093-1
	100.0	20	2-284093-0
	95.0	19	1-284093-9
	90.0	18	1-284093-8
	85.0	17	1-284093-7
	80.0	16	1-284093-6
	75.0	15	1-282093-5
	70.0	14	1-284093-4
	65.0	13	1-284093-3
	60.0	12	1-284093-2
	55.0	11	1-284093-1
	50.0	10	1-284093-0
	45.0	9	284093-9
	40.0	8	284093-8
	35.0	7	284093-7
	30.0	6	284093-6
	25.0	5	284093-5
	20.0	4	284093-4
	15.0	3	284093-3
	10.0	2	284093-2
DIM. A			NO OF POS.
			PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 10SEP2001	TE TE Connectivity								
DIMENSIONS: mm		CHK D. BIEVENOUR 10SEP2001									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 10SEP2001	NAME TERMINAL BLOCK, PCB MOUNT TOP ENTRY WIRE, STACKING W/INTERLOCK, 5.00mm PITCH								
		PRODUCT SPEC 108-20166									
0 PLC ±. 1 PLC ±.3 2 PLC ±.25 3 PLC ±. 4 PLC ±. ANGLES ±2		APPLICATION SPEC 114-20079	SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		
MATERIAL 		FINISH 	WEIGHT -		A3		00779		C-284093		
CUSTOMER DRAWING						SCALE 4:1		SHEET 1		OF 2	
										REV E	

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.

LOC FT	DIST 0	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

NOTES:



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2. MECHANICAL
WIRE STRIPPING LENGTH : 5.0-6.0 mm
MIN. PC BOARD HOLES DIAMETER : 1.1 mm
MAX. PC BOARD THICKNESS : 2.4 mm
RECOMMENDED TIGHTENING TORQUE FOR SCREW : 0.5 Nm.

3. ELECTRICAL
WIRE RANGE : 16-30 AWG
MAX. VOLTAGE : 300 V
MAX CURRENT : 13.5 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)

4. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.




NOT CUMULATIVE TOLERANCE.

6. PART COMPLIES WITH EN 60335-1.

7. PACKED IN TRAY.



OBSOLETE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 10SEP2001		 TE Connectivity											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK D. BIEVENOUR 10SEP2001		NAME TERMINAL BLOCK, PCB MOUNT TOP ENTRY WIRE, STACKING W/INTERLOCK, 5.00mm PITCH									
		0 PLC ±- 1 PLC ±.3 2 PLC ±.25 3 PLC ±- 4 PLC ±- ANGLES ±2		APVD D. BIEVENOUR 10SEP2001											
				PRODUCT SPEC 108-20166											
MATERIAL		FINISH		APPLICATION SPEC 114-20079		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
				WEIGHT -		A3		00779		C-284093		-			
				CUSTOMER DRAWING										SCALE 4:1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[284093-6](#)