




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REDRAWN PER ECO-17-007400	15DEC2017	RS	DR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



1 FOR $\phi 2.921[\phi .115]$ TO $\phi 4.318[\phi .170]$ WIRE INSULATION.

2 BODY MATERIAL THICKNESS: $0.787 \pm 0.051[.031 \pm .002]$

3 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

4 STAMP AMP 16-14* APPROX AS SHOWN.

5 MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B152
INSULATION: NYLON

6 FINISH:
BODY & SLEEVE: TIN PLATE PER ASTM B545
INSULATION: COLOR-BLUE.


5000	ON TAPE	2-320306-1
1000	LOOSE PIECE	320306
QTY	PACKAGE TYPE	PART NO

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity

DIMENSIONS: mm [INCHES]		DWN RAVI S	15DEC2017	MATERIAL 5		FINISH 6	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 5°		CHK ROHDE DANIEL F	15DEC2017	<div>TE</div> <div>TE Connectivity</div>			
		APVD ROHDE DANIEL F	15DEC2017				
		PRODUCT SPEC UL 486 A-B		NAME WIRE TERMINAL, P.I.D.G - HOOK, WIRE SIZE: 16-14			
		APPLICATION SPEC 114-2157					
		WEIGHT —		SIZE A4	CAGE CODE 00779	DRAWING NO C-320306	RESTRICTED TO —
		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[320306](#)