














LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14						
		N1		REVISED PER ECO-19-007720	21MAY2020	KR	DR







STYLE A



STYLE B  
INSULATION RESTRICTING

	100	LOOSE PIECE, BOX	16-14*	2.667[.105]-3.810[.150]	16-14	--	A			8-320564-1
	500	320564 ON TAPE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A			2-320564-3
	500	LOOSE PIECE	14*	1.981[.078]-3.302[.130]	14	GREEN	B			 2-320564-2
	500	LOOSE PIECE	16*	1.600[.063]-3.302[.130]	16	BLUE	B			 2-320564-1
	500	LOOSE PIECE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A			 320564
	QTY	PACKAGE TYPE	 STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY	SLEEVE	PART NO
								FINISH		

CUSTOMER SERVICE SYSTEMS			MAX. RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH CHK T MICHIELUTTI APVD T MICHIELUTTI PRODUCT SPEC UL 486 A-B  APPLICATION SPEC 114-2157 WEIGHT -		 TE Connectivity								
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 VOLT MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:   0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127(.005) 4 PLC ± - ANGLES ± ±		NAME		TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 16-14 AWG PIDG IR 16 & 14 AWG						
FOR APPLICATION		TOOLING ASSISTANCE CENTER		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED OR SOLID		MATERIAL 		FINISH SEE TABLE INSULATION: COLOR-BLUE		SIZE A2		CAGE CODE 00779		DRAWING NO C-320564		RESTRICTED TO -		
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						CUSTOMER DRAWING			SCALE 5:1		SHEET 1 of 1		REV N1	

- 1 STAMP "AMP - SEE TABLE" APPROX AS SHOWN.
- 2 WIRE INSULATION DIA: SEE TABLE.
- 3 BODY MATERIAL THK: 0.787[.031]±0.051[.002].
- 4 BODY: TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545.
- 5 SLEEVE: TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545.
- 6 BODY & SLEEVE- CU PER ASTM B152 INSULATION - NYLON PER ASTM D4066
- 7 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 8 MEETS MS25036-110, CLASS 1 & 2.
- 9 MEETS M7928/1-45, CLASS 1 & 2.
- 10 MEETS M7928/1-54, CLASS 1 & 2.
- 11 UL LISTED
- 12 CSA CERTIFIED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-320564-2](#)