




| REVISIONS |     |             |           |     |      |
|-----------|-----|-------------|-----------|-----|------|
| P         | LTR | DESCRIPTION | DATE      | DWN | APVD |
|           | A   | NEW DRAWING | 01AUG2022 | BDA | DH   |
|           |     |             |           |     |      |
|           |     |             |           |     |      |
|           |     |             |           |     |      |

GENERAL TOLERANCES

HEIGHT & WIDTH : UP TO 2.0mm:   ±0.5mm  
                                  2.1 TO 10.0mm: ±0.8mm  
                                  10.1mm & UP:   ±1.5mm



ISOMETRIC VIEW (NTS)

| 4.8    | 12.7   | 25000 | 236-0048-0127     | STAINLESS STEEL (S/S+)             | 2423884-1   |
|--------|--------|-------|-------------------|------------------------------------|-------------|
| 3.2    | 9.5    | 25000 | 236-0032-0095     | STAINLESS STEEL (S/S+)             | 2423883-1   |
| 3.2    | 6.4    | 25000 | 236-0032-0064     | STAINLESS STEEL (S/S+)             | 2423882-1   |
| 4.8    | 12.7   | 25000 | 234-0048-0127     | TIN PLATED COPPER CLAD STEEL (TCS) | 2423881-1   |
| 3.2    | 9.5    | 25000 | 234-0032-0095     | TIN PLATED COPPER CLAD STEEL (TCS) | 2423880-1   |
| 3.2    | 6.4    | 25000 | 234-0032-0064     | TIN PLATED COPPER CLAD STEEL (TCS) | 2423879-1   |
| 4.8    | 12.7   | 25000 | 232-0048-0127     | MONEL ALLOY 400 WIRE (MON)         | 2423878-1   |
| 3.2    | 9.5    | 25000 | 232-0032-0095     | MONEL ALLOY 400 WIRE (MON)         | 2423877-1   |
| 3.2    | 6.4    | 25000 | 232-0032-0064     | MONEL ALLOY 400 WIRE (MON)         | 2423876-1   |
| 4.8    | 12.7   | 250   | 236-0048-0127-S   | STAINLESS STEEL (S/S+)             | 2423829-1   |
| 3.2    | 9.5    | 250   | 236-0032-0095-S   | STAINLESS STEEL (S/S+)             | 2423828-1   |
| 3.2    | 6.4    | 250   | 236-0032-0064-S   | STAINLESS STEEL (S/S+)             | 2423827-1   |
| 4.8    | 12.7   | 250   | 234-0048-0127-S   | TIN PLATED COPPER CLAD STEEL (TCS) | 2423826-1   |
| 3.2    | 9.5    | 250   | 234-0032-0095-S   | TIN PLATED COPPER CLAD STEEL (TCS) | 2423825-1   |
| 3.2    | 6.4    | 250   | 234-0032-0064-S   | TIN PLATED COPPER CLAD STEEL (TCS) | 2423824-1   |
| 4.8    | 12.7   | 250   | 232-0048-0127-S   | MONEL ALLOY 400 WIRE (MON)         | 2423823-1   |
| 3.2    | 9.5    | 250   | 232-0032-0095-S   | MONEL ALLOY 400 WIRE (MON)         | 2423822-1   |
| 3.2    | 6.4    | 250   | 232-0032-0064-S   | MONEL ALLOY 400 WIRE (MON)         | 2423821-1   |
| CORE H | CORE W | L     | ALIAS PART NUMBER | MATERIAL                           | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED

±

±

±

±

±

±

±

MATERIAL

SEE TABLE

DWN

CHK

APVD

NAME

DATE

BASAVARAJA D A

B.SELVAPANDIAN

D. HEMMINGS

01AUG2022

01AUG2022

01AUG2022

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

SCALE

4:1

RESTRICTED TO

-

TE Connectivity

23X-RECT SILICONE SPONGE CORE

RECTANGULAR-SS-CORE

SHEET 1 OF 1

REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TE Connectivity:

[232-0032-0064](#) [232-0032-0095](#) [232-0048-0127](#) [234-0032-0064](#) [234-0032-0095](#) [234-0048-0127](#) [236-0032-0064](#)  
[236-0032-0095](#) [236-0048-0127](#)