

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		REVISIONS					
© COPYRIGHT — TE Connectivity		ALL RIGHTS RESERVED.		P	LTR	DESCRIPTION	DATE	DWN	APVD
					L	REV PER 0G3A-0256-04	08APR04	JR	MS
					L1	REVISED PER ECO-17-006294	13OCT2017	RS	DR

STAMPING DETAIL

1 FOR  $\varnothing$ 5.97 [ $\varnothing$ .235] MAX WIRE INSULATION.

2 MATERIAL: BODY — COPPER  
INSULATION — PVC

3 FINISH: BODY — TIN PLATE PER ASTM B-545  
INSULATION — YELLOW

500	LOOSE PC	34308
QTY	DESCRIPTION	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 90°C[194°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G KRUPER 1/93	TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK R HERSEY 1/93					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm²[5180-13100] SOLID OR STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD M ELLIS 1/93	NAME SPLICE, WIRE, CLOSED END 22-10 AWG				
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	MATERIAL 2	FINISH 3	PRODUCT SPEC —					
					APPLICATION SPEC —	SIZE A3	CAGE CODE 00779	DRAWING NO C-34308	RESTRICTED TO —	
					WEIGHT —	CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV L1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34308](#)