



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	17JUN2015	DL	CW
	B	ECR-20-014876	21JUL2021	WQR	CW



TYPE I: BODY + PLASTIC PROTECITON COVER






NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, GRAY
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
主体材料: 铝合金
表面处理: 粉末喷涂, 灰色
防护等级: IP65(配合)

TI460240121-000	TYPE I	H24B-SDR-BO-PG2I	PG2I	-
TI460240125-000		H24B-SDR-BO-M25	M25	-
TI460240221-000		H24B-SDR-BO-2PG2I	PG2I	PG2I
TI460240225-000		H24B-SDR-BO-2M25	M25	M25
ASSEMBLY PART NUMBER	TYPE	ASSEMBLY PART DESCRIPTION	IG1	IG2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17JUN2015	TE Connectivity	
		DAVID LI			
		CHK	17JUN2015		
		CHRIS WANG			
		APVD	17JUN2015	NAME H24B-SDR-BO-PG/M	
		XU XIANG			
		PRODUCT SPEC			
		108-137013			
		APPLICATION SPEC		SIZE A3	
		114-137013			
		WEIGHT	-		
		CUSTOMER DRAWING			
		SCALE	3:5	SHEET	1 OF 2
		REV	B		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



TYPE 2: BODY + METAL PROTECITON COVER
OTHER SPEC REFER TO TYPE 1

TI460241121-000	TYPE 2	H24B-SGRM-BO-PG21	PG21	-
TI460241125-000		H24B-SGRM-BO-M25	M25	-
TI460241221-000		H24B-SGRM-BO-2PG21	PG21	PG21
TI460241225-000		H24B-SGRM-BO-2M25	M25	M25
ASSEMBLY PART NUMBER	TYPE	ASSEMBLY PART DESCRIPTION	IG1	IG2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

-

DWN DAVID LI 17JUN2015

CHK CHRIS WANG 17JUN2015

APVD XU XIANG 17JUN2015

PRODUCT SPEC 108-137013

APPLICATION SPEC 114-137013

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME H24B-SGRM-BO-PG/M

SIZE A3

CAGE CODE -

DRAWING NO. ©-TI46024XXXX000

RESTRICTED TO

SCALE 3:5 SHEET 2 OF 2 REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T1460241125-000](#)