

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - By -				ALL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
					M1	REVISED PER ECO-14-001427	29JAN2014	NK	DR

AMP

WIRE RANGE

22-10 AWG
SOLID OR STRANDED

UL

Listed

22-10 AWG
SOLID OR STRANDED

LR7189

Certified

22-10 AWG
SOLID OR STRANDED

SA

AMP

2210

VS

UL

STAMPING DETAIL

1

FOR 7.62[.300] MAX WIRE INSULATION DIAMETER.

BODY

INSULATION

25.65

[1.010]

MAX

50

LOOSE PC, BOX

8-34865-2

500

LOOSE PC

34865

QTY

DESCRIPTION

PART NUMBER

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
90°C [194°F] MAX

VOLTAGE RATING:
300V MAX

WIRE:
2.62-6.64mm² [5180-13100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
BODY: COPPER
INSULATION: PVC
COLOUR: YELLOW

FINISH
SPLICED: TIN PLATED
ASTM B545

DWN
G KRUPER
1/93

CHK
R HERSEY
1/93

APVD
M CLINE
1/93

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

TE Connectivity

NAME
SPlice, WIRE, CLOSED END

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-34865

RESTRICTED TO

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
M1

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34865](#)