

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	15APR2015	DL	CW
	AI	ECR-15-009224	23JUN2015	DL	CW
	B	ECR-15-018481	22FEB2016	DL	CW
	C	ECR-21-111798	09SEP2021	WQR	CW

NOTES:




1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: POWER: CONDUCTOR - GROUND: 230 V
CONDUCTOR - CONDUCTOR: 400 V
SIGNAL: 160 V
RATED CURRENT: POWER: 16 A; SIGNAL: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: POWER: 4 KV; SIGNAL: 2.5 KV
POLLUTION DEGREE: 2
FLAMMABILITY: UL94V-0
MATING CYCLES: 500
OPERATION TEMPERATURE: $-40-+125^{\circ}C$
WIRE RANGE: POWER: 0.14-4.0 mm² (26-12 AWG)
SIGNAL: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: 16A: T20300X20XX000;
10A: T20200X20XX000)

注释:



1. 技术参数:
绝缘材料: PC
额定电压: 电源: 导体-地: 230 V; 导体-导体: 400 V; 信号: 160 V
额定电流: 电源: 16 A; 信号: 10 A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 电源: 4 KV; 信号: 2.5 KV
污染等级: 2
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40-+125^{\circ}C$
接线范围: 电源: 0.14-4.0 mm² (26-12 AWG);
信号: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
2. 端子需要单独订购.
(订货号参考图面: 16A: T20300X20XX000; 10A: T20200X20XX000)



M5 THREAD
RECOMMENDED TIGHTENING TORQUE 2.0Nm



4 X M3 THREAD
RECOMMENDED TIGHTENING TORQUE 0.5Nm



PANEL CUT OUT FOR INSERTS FOR USING
WITHOUT HOODS/HOUSINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN DAVID LI 15APR2015

CHK CHRIS WANG 15APR2015

APVD XU XIANG 15APR2015

PRODUCT SPEC

108-137131

APPLICATION SPEC

114-137131

WEIGHT -

CUSTOMER DRAWING

T2100322201-000

HK8/24-032-F
HK8/24-032 母插

PART NUMBER

料号

PART DESCRIPTION

描述

STE

TE Connectivity

NAME

HDC-HK8/24-032-F

SIZE

A3

CAGE CODE

-

DRAWING NO

©-T2100322201000

RESTRICTED TO

SCALE

1:1

SHEET

OF

1

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2100322201-000](#)