




LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN
CM	00	M2		REVISED PER ECR-12-011660	28JAN13	KH

- 1 PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- 2 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 5 SUPERSEDED BY 350836-4



RECOMMENDED LAYOUT FOR 3.18 [.125] THICK PC BOARD

5	PH BRZ GOLD 4	NYLON,94V-0	350836-4
	PH BRZ GOLD 2	NYLON,94V-0	350836-2
	PH BRZ TIN	NYLON,94V-0	350836-1
	CONTACT	HOUSING	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC ±		1 PLC ±	
1 PLC ±		2 PLC ±	
2 PLC ±		3 PLC ± 0.13 [.005]	
3 PLC ±		4 PLC ±	
4 PLC ±		ANGLES	
MATERIAL SEE TABLE		FINISH SEE TABLE	
WEIGHT		APPLY SPEC	
CUSTOMER DRAWING		SCALE 5:1	
SHEET 1 OF 1		REV M2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[350836-1](#)