




CODE 15 - TINEL-LOCK BACKSHELL









TXR15AB00-1608AI-

SERIES _____
 TXR: RING INCLUDED
 (SEE RING OPTION)
 TX: RING NOT INCLUDED
 CONNECTOR INTERFACE _____
 MATERIAL _____
 REFER TO CH00-0250-008
 FINISH _____
 REFER TO CH00-0250-008
 ANGLE _____
 DASH NUMBER (TABLE 1) _____
 ENTRY SIZE (TABLE 2) _____
 RING OPTION _____
 AI - TO SUIT SINGLE BRAID
 BI - TO SUIT DOUBLE BRAID
 FOR TX, LEAVE BLANK
 MODIFICATION CODE _____
 REFER TO CH00-0250-008 2

NOTES:

1. THIS PRODUCT IS DESIGNED TO TERMINATE A BRAIDED CABLE SHIELD AND A HEAT SHRINKABLE LIPPED BOOT TO A CONNECTOR.
- 2 FOR ADDITIONAL DIMENSIONS, ORDERING INFORMATION AND MODIFICATIONS, SEE CH00-0250-008.
- 3 SEE DRAWING TR FOR DETAIL ON TINEL-LOCK RING, RINGS ARE DESIGNED TO BE HEATED ELECTRICALLY, ALL RINGS ARE MARKED WITH THERMOCHROMIC PAINT WHICH CHANGES COLOUR WHEN INSTALLATION TEMPERATURE IS REACHED.
4. BACKSHELL TO BE PERMANENTLY MARKED/BAGGED AND LABELLED WITH CODE IDENTIFICATION NUMBER AND PART NUMBER LESS RING DESIGNATOR. (e.g. 06090-TXR15AB00-1206). RING SHALL BEAR NO MARKING.
- 5 IF MAX ENTRY IS EXCEEDED, A 2 PIECE BACKSHELL ASSEMBLY (TYPE 2) IS SUPPLIED.
6. BACKSHELL MATES TO MIL-C-5015, SOLDER CONTACT, MS3100, MS3101, MS3106, MS3107 AND MS3108 WITH ENDBELL.
- 7 ANTI-ROTATIONAL SET SCREW, THREE THREADED HOLES $120^\circ \pm 5^\circ$ APART, SINGLE MATING SET SCREW SUPPLIED.

DRAWN	K.WINCZURA	DATE	04/12/2014	 3RD ANGLE PROJECTION NOT TO SCALE UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	TITLE: TINEL-LOCK BACKSHELL		 Polamco 	
CHECKED		DATE	04/12/2014					
APPROVED	K.SHEPPARD	DATE	11/12/2014					
APPROVED	H.SMITH	DATE	07/07/2015					
REVISIONS					ASSY USED ON: MIL-C-5015 MS "V" THREAD END BELLS		TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.	
LTR	DESCRIPTION	DATE	APPROVED					
E	REVISED PER ECO-15-009981	07/07/2015	H.SMITH					
F	REVISED PER ECO-18-002419	03/04/2018	D.JONES					
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792					DRAWING NO: TXR15		DRAWING REV: F	SHT 1



DRAWN	K.WINCZURA	DATE	04/12/2014
CHECKED		DATE	04/12/2014
APPROVED	K.SHEPPARD	DATE	11/12/2014
APPROVED	H.SMITH	DATE	07/07/2015
REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
E	REVISED PER ECO-15-009981	07/07/2015	H.SMITH
F	REVISED PER ECO-18-002419	03/04/2018	D.JONES
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792			

TITLE:			
TINEL-LOCK BACKSHELL			
ASSY USED ON:			
MIL-C-5015 MS "V" THREAD END BELLS			
TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.		DRAWING NO: TXR15	DRAWING F

 Polamco  TE connectivity			
DRAWING NO:	DRAWING REV:	SHT	
TXR15	F	2	

TABLE 1

										THESE DIMENSIONS APPLY IF BACKSHELL IS STAINLESS STEEL OR NICKEL ALUMINIUM BRONZE		
ORDER NUMBER	SHELL SIZE	A THREAD	ØB MAX	MAX ENTRY	C ±0,5	D ±0,5	W ±0,5	T ±0,5	E MAX	W MAX	T ±0,5	E MAX
03	8S & 10S	1/2-28UNEF	21,5	05	12,6	27,5	21,7	13,5	28,5	22,2	15,0	28,5
04	10SL,12 & 12S	5/8-24UNEF	25,0	07	14,0	28,0	24,9	15,9	30,0	25,4	16,5	30,0
06	14 & 14S	3/4-20UNEF	28,0	08	15,0	29,0	27,9	17,9	31,5	28,4	17,9	31,5
08	16 & 16S	7/8-20UNEF	31,1	10	15,6	29,7	31,3	19,3	33,2	31,8	20,1	33,2
10	18	1-20UNEF	35,0	12	16,3	30,5	34,3	21,3	34,8	34,8	21,3	34,8
12	20 & 22	1 3/16-18UNEF	39,0	16	17,2	30,9	40,4	22,9	36,3	40,9	22,9	36,3
16	24 & 28	1 7/16-18UNEF	45,2	20	17,9	32,1	46,5	27,0	39,4	44,5	27,0	39,4
20	32	1 3/4-18UNS	54,9	24	24,3	32,1	53,3	30,7	43,3	50,8	32,0	43,3
24	36	2-18UNS	62,0	24	26,9	29,3	57,8	32,8	47,3	58,3	34,8	47,3
28	40	2 1/4-16UN	68,6	24	31,8	30,7	64,4	36,5	51,5	64,9	38,9	51,5

TABLE 2

										THESE DIMENSIONS APPLY IF BACKSHELL IS STAINLESS STEEL OR NICKEL ALUMINIUM BRONZE		
ENTRY SIZE	ØZ MIN	ØS	ØY ±0,3	ØK MAX	F ±0,5	G ±0,5	H ±0,5	M ±0,5	J ±0,5	H ±0,5	M ±0,5	J ±0,5
04	6,35	9,49 +/-0,04	14,00	NA	NA	NA	NA	NA	NA	NA	NA	NA
05	7,92	11,06 +/-0,04	15,50	NA	NA	NA	NA	NA	NA	NA	NA	NA
06	9,53	12,66 +/-0,04	17,10	21,0	12,5	27,5	24,0	15,5	27,95	24,3	17,2	28,2
07	11,10	14,21 +/-0,07	18,70	21,0	12,5	27,5	24,0	15,5	27,95	24,3	17,2	28,2
08	12,70	15,81 +/-0,07	20,30	24,5	13,1	28,0	27,0	17,0	29,45	28,3	19,4	29,7
10	15,88	18,96 +/-0,08	23,50	29,0	13,5	29,0	31,0	19,5	31,00	31,1	21,0	31,2
12	19,05	22,14 +/-0,08	26,70	32,5	14,5	29,7	34,0	21,0	32,70	34,2	22,8	32,9
14	22,23	25,30 +/-0,08	29,80	35,5	15,5	30,5	35,0	20,0	34,25	38,5	25,3	34,5
16	25,40	28,48 +/-0,08	33,00	37,0	16,1	30,9	38,0	21,5	35,80	40,7	26,1	36,1
18	28,58	31,65 +/-0,08	36,20	40,0	16,5	31,1	42,0	24,0	37,40	43,7	27,6	37,6
20	31,75	34,83 +/-0,08	39,40	43,5	17,0	32,1	45,0	25,5	38,90	46,4	29,1	39,1
22	34,93	37,98 +/-0,08	42,50	48,5	18,5	35,3	54,5	31,0	42,00	50,0	31,0	42,0
24	38,10	41,15 +/-0,08	45,70	52,1	21,9	38,1	58,0	33,0	46,00	53,5	33,0	46,0

DRAWN	K.WINCZURA	DATE 04/12/2014	 3RD ANGLE PROJECTION NOT TO SCALE UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°	TITLE:				 Polamco 		
CHECKED		04/12/2014		TINEL-LOCK BACKSHELL ASSY USED ON: MIL-C-5015 MS "V" THREAD END BELLS						
APPROVED	K.SHEPPARD	11/12/2014								
APPROVED	H.SMITH	07/07/2015								
REVISIONS				TE CONNECTIVITY - POLAMCO LTD RESERVES THE RIGHT TO AMEND THIS DRAWING AND THE INFORMATION SET FORTH HEREON AT ANY TIME. USERS SHOULD INDEPENDENTLY EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.				DRAWING NO: TXR15	DRAWING REV: F	SHT 3
LTR	DESCRIPTION	DATE	APPROVED							
E	REVISED PER ECO-15-009981	07/07/2015	H.SMITH							
F	REVISED PER ECO-18-002419	03/04/2018	D.JONES							
TE CAGE CODE: 06090 POLAMCO/TE CAGE CODE: U5792										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[TXR15AZ00-2014AI](#) [TXR15AB00-1612AI](#) [TXR15AB45-1610AI](#) [TXR15AB90-1610AI](#) [TXR15AB00-1208AI](#)
[TXR15AB00-1212AI](#) [TXR15AB00-2014AI](#) [TXR15AB00-2416AI](#) [TXR15AB00-1005AI](#) [TXR15AB00-1205AI](#)
[TXR15AB00-1618AI](#) [TXR15AB00-2412AI](#) [TXR15AZ00-1006AI](#) [TXR15AB00-1008AI2](#) [TXR15AB00-1212AIH](#)
[TX15AB00-2414](#) [TX15AB00-1010](#) [TX15AB00-2416](#) [TX15AB00-2412](#) [TX15AB45-1610](#) [TX15AB90-2416](#) [TX15AB00-1212H](#) [TXR15AB00-1212AI2](#) [TX15AB00-1214](#) [TXR15AB00-1614AI2](#) [TXR15AB00-1012AIH](#) [TXR15AB90-2416AI](#)
[TXR15AB00-2414AI](#) [TX15AB00-1618H](#) [TXR15AB00-1008AI-CS2205](#) [TXR15AB00-0808AI2](#) [TXR15AB00-1216AIH](#)
[TX15AB00-1012H](#) [TXR15AB00-1618AIH](#) [TXR15AB00-1612AI2](#) [TXR15AZ00-1008BI](#) [TX15AB00-0604](#) [TX15AB00-1212](#) [TX15AB00-1008-CS2205](#) [TX15AZ00-1608](#) [TX15AB00-1005](#) [TX15AZ00-1006](#) [TX15AB00-1008](#) [TX15AB45-0808](#) [TX15AB00-0812](#) [TX15AB00-0404](#) [TX15AB00-2424](#) [TX15AB90-1610](#) [TX15AB00-1614](#) [TX15AB00-1618](#)
[TX15AB00-1610](#) [TX15AB00-1612](#) [TX15AB00-2016](#) [TX15AB00-2014](#) [TX15AB00-1620](#) [TX15AB00-1216H](#)
[TX15AB00-2024](#) [TX15AB00-2820](#) [TX15AB00-0808](#) [TX15AB00-1210](#) [TX15AB00-1207](#) [TX15AB00-1205](#) [TX15AB00-1208](#) [TX15AB00-1204](#) [TX15AB00-0608](#) [TX15AZ45-2422](#) [TXR15AC45-2422AI](#) [TXR15AZ00-1608AI](#) [TXR15AZ00-1610AI](#) [TXR15AB00-1008BI](#) [TXR15AB00-1620AI](#) [TXR15AB90-2012AI](#) [TXR15AZ00-0608BI](#) [TXR15AZ00-1010BI](#)
[TXR15AB45-1608AI](#) [TXR15AB00-0808AI](#) [TXR15AB00-0404AI](#) [TXR15AB00-1010AI](#)