


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



- 1 WIRE INSULATION DIA. = SEE TABLE, DIM. "A"
- 2 TONGUE MATERIAL THK. = .040 $\pm$.002
- 3 BODY FINISH: TIN PLATE (MIL-T-10727).000100 MIN THK

OBSOLETE

OBSOLETE

REVISIONS				DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION	
✓			D	REDRAWN-REVISED PER G-1477.	3/11/82 Pjm
✓			E	G-1175, P87-0087 & P85-C0891G-1928	3/24/87 GS
✓			F	OBSOLETE -4 PER G-2393	4-12-88 MGL/44
✓			F	REVISED G-3044	5/6/88 GY
✓			G	OBS -5 PER G-3358	11/3/91 DKS/712
✓			H	REV PER G-5648	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS $\pm .005$ ANGLES $\pm 1^\circ$		CONTRACT NO		NAME	
MATERIAL INSULATION: NYLON - YELLOW		DR UTA / RFB 9-26-85		AMP AMP INCORPORATED Harrisburg, Pa.	
SLEEVE: COPPER (QQ-C-576)		CHK: [Signature] 12-19-86		TERMINAL SPADE	
BODY: PHOSPHOR BRONZE (QQ-B-750)		APPD: [Signature] 2-19-86		P.I.D.G., SPRING WIRE SIZE: 12-10	
DSGN APPD		SIZE		FSCM NO	
OTHER APPD		B		00779	
		SCALE NTS		DRAWING NO 52430	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[52430](#)