

4


3


2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT — TE Connectivity Ltd.	ALL RIGHTS RESERVED.




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REV PER 0G3A-0668-04	24AUG04	JR	TM
	N1	REVISED PER ECO-17-014338	28MAR2018	RS	DR
	N2	REVISED PER ECO-18-015550	04OCT2018	RS	DR



AMP WIRE RANGE	 Listed FILE E13288
12-10 AWG SOLID OR STRANDED	12 AWG STRANDED

- 1 STAMP 8S AMP 12-10* APPROX AS SHOWN
- 2 SEE TABLE FOR WIRE INSUL DIA
- 3 BODY MATL THK, 1.016±.051[.040±.002]
- 4 MATERIAL: BODY — BRASS PER ASTM B36
INSULATION — PVC.
- 5 APPLIES FROM CENTER OF STUD HOLE TO
EDGE OF METAL WIRE BARREL

28.219 [1.111]	23.774 [.936]	6.350-7.620 [.250-.300]	1500	ON TAPE, REEL	52962-3
28.219 [1.111]	23.774 [.936]	6.350-7.620 [.250-.300]	500	LOOSE PIECE	52962-2
26.721 [1.052]	22.276 [.877]	2.667-5.080 [.105-.200]	2500	ON TAPE, REEL	52962-1
26.721 [1.052]	22.276 [.877]	2.667-5.080 [.105-.200]	500	LOOSE PIECE	52962
L	E	WIRE INSUL DIA	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			<div></div> TE Connectivity Ltd.				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		<div><div>DIMENSIONS: mm [INCHES]</div><div></div></div>	<div><div>TOLERANCES UNLESS OTHERWISE SPECIFIED:</div><div><div>0 PLC ± -</div><div>1 PLC ± -</div><div>2 PLC ± -</div><div>3 PLC ± 0.127[.005]</div><div>4 PLC ± -</div><div>ANGLES ± -</div></div></div>	DWN L OLMEDA 26JUN95		NAME TERMINAL, SPRING SPADE, SHORT, PLASTI-GRIP WIRE SIZE 12-10			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED				CHK M ELLIS 26JUN95					
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	<div><div>MATERIAL</div><div></div></div>	FINISH BODY: TN PER ASTM B545 INSULATION: COLOR=YELLOW	APVD G NGO 26JUN95		SIZE A3	CAGE CODE 00779		DRAWING NO C-52962	RESTRICTED TO —	
					PRODUCT SPEC UL 486A-B							
					APPLICATION SPEC 114-2161							
					WEIGHT		CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1	REV N2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[52962-2](#)