



intercontec
products

Kontaktstift ø10 mm

Einsatzbereich: - 958 Kupplung / Einbaudose
Crimp 10 mm²

TE Teile Nr.: 61-0112-023-000
IC Ref. Nr.: 61.112.23

Elektrische Werte

Bemessungsstrom max. 78 A*
Durchgangswiderstand < 90 µOhm

Werkstoff

Kontakt Messing, versilbert

Anschluss

Anschlussart/-bereich Crimp/ 10 mm²
max. Litzenaußendurchmesser ø14,8 mm
Abisolierlänge 17 mm
Crimpeinstellungen sind individuell zu wählen


Mechanische Werte

Steckzyklen 500

Werkzeuge (nicht im Lieferumfang enthalten)

Akku-Crimpzange TE Teile Nr.: C0-0207-000-000
IC Ref. Nr.: C0.207.00

(Crimpbacken für 10 mm Kontakt TE Teile Nr.: C0-0211-000-000
IC Ref. Nr.: C0.211.00)



Hauptabmessungen

Kontaktstift

Y6-D530-000-00DE erstellt: 16.03.2012/MH geändert: 11.10.2018/RN

© 2018 TE Connectivity.

TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* Bei max. Anschlussquerschnitt



intercontec
products

Contact Pin $\varnothing 10$ mm

for: - 958 Extension / Receptacle
crimp 10 mm^2

TE part number: 61-0112-023-000
IC reference number: 61.112.23

Electrical Data

rated current max. 78 A*
contact resistance $< 90 \mu\text{Ohm}$

Material

contact brass, silver plated

Termination

cross-section crimp/ 10 mm^2
max. outer wire diameter $\varnothing 14.8 \text{ mm}$
stripping length 17 mm
crimp settings select individually


Mechanical Data

mating cycles 500

Tools (not part of production contents)

battery crimp tool TE part no.: C0-0207-000-000
IC ref. no.: C0.207.00

(crimping insert for 10 mm contact TE part no.: C0-0211-000-000
IC ref. no.: C0.211.00)



Main Dimensions
contact pin

Y6-D530-000-00EN issued: 16.03.2012/MH; modified: 11.10.2018/RN

© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* for max. wire cross-section

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[61.112.23](#)