

SPECIFICATION CONTROL DRAWING

SCD

55LF0812

Title

WIRE, RADIATION-CROSSLINKED, MODIFIED ETFE-INSULATED,
ULTRA LOW FLUORIDE, NORMAL WEIGHT, GENERAL PURPOSE, 600 VOLT

Date

10-16-18

Revision

C

This specification sheet forms a part of the latest issue of Raychem Specification 55A.




TABLE I. CONSTRUCTION DETAILS

PART NUMBER 1/	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	DIAMETER OF STRANDED CONDUCTOR (inch)		FINISHED WIRE		
			MINIMUM	MAXIMUM	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (inch)	MAXIMUM WEIGHT (lbs/1000 ft.)
55LF0812-26-*	26	19 x 38	.018	.019	38.4	.040 ± .002	1.7
55LF0812-24-*	24	19 x 36	.023	.024	24.3	.045 ± .002	2.3
55LF0812-22-*	22	19 x 34	.029	.030	15.1	.050 ± .002	3.3
55LF0812-20-*	20	19 x 32	.037	.038	9.19	.058 ± .002	4.7
55LF0812-18-*	18	19 x 30	.046	.048	5.79	.070 ± .003	7.2
55LF0812-16-*	16	19 x 29	.052	.054	4.52	.077 ± .003	9.0
55LF0812-14-*	14	19 x 27	.065	.068	2.88	.094 ± .003	13.8
55LF0812-12-*	12	37 x 28	.084	.087	1.90	.111 ± .003	20.5
55LF0812-10-*	10	37 x 26	.106	.112	1.19	.134 ± .004	32.4

TABLE II. PERFORMANCE DETAILS

PART NUMBER 1/	MANDREL DIAMETER (inch) (± 3%)		WEIGHT (lb) (± 3%)	
	IMMERSION, LIFE CYCLE, AND ACCELERATED AGING	COLD BEND	IMMERSION, LIFE CYCLE, AND ACCELERATED AGING	COLD BEND
55LF0812-26-*	.375	1.00	.500	3.00
55LF0812-24-*	.500	1.00	.750	3.00
55LF0812-22-*	.500	1.00	1.00	3.00
55LF0812-20-*	.500	1.00	1.50	4.00
55LF0812-18-*	.750	1.50	2.00	4.00
55LF0812-16-*	1.00	1.50	2.00	5.00
55LF0812-14-*	1.00	2.00	3.00	5.00
55LF0812-12-*	1.50	2.00	3.00	5.00
55LF0812-10-*	2.00	3.00	3.00	5.00

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-881, EXCEPT LIGHT COLORS SHALL BE DESIGNATED
WITH AN "L" AFTER THE COLOR CODE (0L, 1L, 2L, etc.). OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER,
AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.





WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING (CROSSLINKING PROOF): 300 ± 3°C for 7 hours

BLOCKING: 230 ± 3°C for 24 hours

CONCENTRICITY: 70% (minimum)

FLAMMABILITY: Procedure 1,

3 seconds (maximum), 3 inches (maximum); no flaming of facial tissue

FLUORIDE EXTRACTION: 70 ± 2°C for 168 hours, 20 ppm (maximum)

HUMIDITY RESISTANCE: Insulation Resistance, 5000 megohms for 1000 ft. (minimum)

IDENTIFICATION, COLOR STRIPING, AND BAND DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

IMMERSION: Diameter increase 5% (maximum); no cracking, no dielectric breakdown

INSULATION ELONGATION AND TENSILE STRENGTH:

Primary Insulation,

Elongation, 125% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

Total Insulation (primary insulation and jacket),

Elongation, 75% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

INSULATION FLAWS:

Primary Insulation,

Spark Test, 1.5 kV (rms) at 60 Hz; 4.2 kV (rms) at 3 kHz

Impulse Dielectric Test, 6.0 kV (peak)

Finished Wire,

Spark Test, 5.7 kV (rms) at 3 kHz

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION RESISTANCE: 5000 megohms for 1000 ft. (minimum)

INSULATION THICKNESS:

0.003 in. (minimum) for primary insulation

0.004 in. (minimum) for outer jacket

0.009 in. (minimum) for total insulation

JACKET COLOR: Per MIL-STD-681, except light colors (xL) shall meet Munsell color limits for UV laser markable wire in SAE AS22759. White preferred.

LIFE CYCLE: 230 ± 3°C for 500 hours

LOW TEMPERATURE-COLD BEND: -65 ± 3°C for 4 hours

SHRINKAGE: 230 ± 3°C for 6 hours, 0.125 in. (maximum) in 12 inches

SMOKE TEST: 250 ± 5°C, no visible smoke

SOLDERABILITY (Quality Conformance):

Per MIL-STD-202, Method 208, except without steam aging

SURFACE RESISTANCE: 500 megohms-in. (minimum), both readings

THERMAL SHOCK RESISTANCE: 200 ± 3°C,

0.060 in. (maximum), AWG 26-12

0.100 in. (maximum), AWG 10

UV LASER MARKING (Test per SAE AS22759, Quality Conformance):

70% (minimum average) for white (9) and light (-xL) insulation colors only

VOLTAGE WITHSTAND (Post Environmental): 2500 volts (rms), 60 Hz

WICKING: 2.25 in. (maximum)

WRAP TEST: 313 ± 3°C for 2 hours

1/ PART NUMBER:

The "***" in the part numbers in Tables I and II shall be replaced by a color code designator.

Example: AWG 22, white: 55LF0812-22-9

AWG 22, light green: 55LF0812-22-5L

AWG 22, white with a black stripe: 55LF0812-22-90

1/ See footer section on page 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EM7119-000](#)