




- 1

0.51µm [.000020] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH GOLD FLASH ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 2

1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 3

0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH GOLD FLASH ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 4

GOLD PLATING NEED NOT APPEAR IN THIS AREA.
- 5

REVERSE REELED FOR MINI-APPLICATOR.
- 6

WIRE RANGE 14-18 AWG.
INSULATION RANGE 2.79[.110]-3.81[.150].
- 7

0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 8

1.27µm [.000050] MIN TIN PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 9

0.38µm [.000015] MIN. GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN. WITH GOLD FLASH ON THE REMINDER, OVER 1.27µm [.000050] MIN. NICKEL PER QQ-N-290.
- 10


PRELIMINARY - NOT FOR PRODUCTION.

- 11

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 12

0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER .76µm[.000030] MIN NICKEL PER QQ-N-290.

11	OBSOLETE	9	CU-NI ALLOY	-	10	1-66598-5
		8	BRASS	-		1-66598-4
		8	PHOSPHOR BRONZE	-		1-66598-3
		8	CU-NI ALLOY	1-66601-2		1-66598-2
		3	CU-NI ALLOY	1-66601-0		1-66598-1
		8	BRASS	-		1-66598-0
		8	BRASS	66601-9		66598-9
		7	BRASS	66601-5		66598-8
		2	BRASS	-		66598-7
		3	PHOSPHOR BRONZE	66601-4		66598-6
11	SUPERSEDED	2	PHOSPHOR BRONZE	66601-3		66598-5
		1	BRASS	-		66598-3
		12	BRASS	66601-2		66598-2
		2	BRASS	66601-1		66598-1
		BODY FINISH		BODY MATERIAL		LOOSE PIECE REF
						PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.HOFFECKER 8-11-88	 TE Connectivity				
		CHK J.McCLINTON 8-11-88					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	NAME SOCKET ASSEMBLY, .062, TYPE III+				
	0 PLC ± —	PRODUCT SPEC —					
	1 PLC ± —	—					
	2 PLC ± —	APPLICATION SPEC					
	4 PLC ± —	—					
MATERIAL	ANGLES ± — FINISH	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=66598	RESTRICTED TO —	
SEE CALLOUTS	SEE CALLOUTS	CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV Z

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-66598-0](#)