




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00						
			L	REVISED PER ECO-10-000073	15FEB2010	CJV	SB



- 1 MOLDED PARTS: FLAME RETARDANT 94V-0 RATED THERMOPLASTIC; BLACK.
SHELLS: CARBON STEEL.
CONTACTS: PHOS BRONZE.
- 2 SHELLS: 5.08µm [.000200] MIN TIN OVER 2.54µm [.000100] MIN COPPER.
- 3 SHELLS: 5.08µm [.000200] MIN BRIGHT TIN OVER 2.54µm [.000100] MIN COPPER. (NO TIN-LEAD)
- 4 CONTACTS: GOLD FLASH ON MATING END, 2.54µm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 CONTACTS: 0.76µm [.000030] MIN GOLD ON MATING END, 2.54µm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL, 0.76µm [.000030] MIN TOTAL ON MATING END, 2.54µm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER 1.27µm [.000050] NICKEL.



OBSOLETE	3 5	4.78 [.188]	1-745183-0
SUPSD 745183-3	2 4	8.43 [.322]	745183-9
SUPSD 745183-7	2 4	4.78 [.188]	745183-8
	2 5	4.78 [.188]	745183-7
OBSOLETE	-	-	745183-6
SUPSD 745183-3	2 5	16.54 [.651]	745183-5
SUPSD 745183-3	2 4	10.85 [.427]	745183-4
	2 5	10.85 [.427]	745183-3
	2 4	3.18 [.125]	745183-2
	2 5	3.18 [.125]	745183-1
FINISH	DIM A	PART NUMBER	



P.C. BOARD MOUNTING DIMENSIONS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 03 AUG 95	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK R.STONE 23 AUG 95		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.TAYLOR 23 AUG 95	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC 108-40005 APPLICATION SPEC 114-40013	RECEPTACLE ASSY, SIZE 1, 9 POS, VERTICAL, AMPLIMITE™HDP	
MATERIAL		WEIGHT -	SIZE A2	RESTRICTED TO -
SEE TABLE		CUSTOMER DRAWING	CAGE CODE 00779	DRAWING NO C=745183
		SCALE NTS	SHEET 1 OF 1	REV L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[745183-1](#)