


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E2	REVISED PER ECO-11-005027	16MAR2011	RK	HMR



1. MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4. WIRE SIZE RANGE: 12-30 AWG.


5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.

6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.



7. NOT CUMULATIVE TOLERANCE.

8. SCREWS BOTTOMED IN TERMINAL BLOCK TO CLOSE CAGE CLAMP.

9. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL
WHERE SPACE PERMITS.



796692-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT

8	83.82	81.28	16	1-796692-6
	17.78	15.24	3	1-796692-3
	63.50	60.96	12	1-796692-2
	58.42	55.88	11	1-796692-1
	53.34	50.80	10	1-796692-0
	48.26	45.72	9	796692-9
	43.18	40.64	8	796692-8
	38.10	35.56	7	796692-7
	33.02	30.48	6	796692-6
	27.94	25.40	5	796692-5
	22.86	20.32	4	796692-4
	17.78	15.24	3	796692-3
12.70	10.16	2	796692-2	
B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 21FEB2002 CHK D. BIEVENOUR 21FEB2002 APVD D. BIEVENOUR 21FEB2002		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2 FINISH		NAME TERMINAL BLOCK, PCB MOUNT 1ST AND 2ND LEVEL STACKING W/INTERLOCK, 5.08mm PITCH	
		PRODUCT SPEC 108-20166		SIZE A2	
MATERIAL		APPLICATION SPEC 114-20079		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-796692	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 3:1 SHEET 1 OF 1 REV F2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[796692-3](#)