

WAR NR. —		LOC	DIST	REVISIONS					
VERWENDET FÜR —		—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, BEHALTEN WIR UNS VOR				S		CONTACT PIN MATERIAL CHANGED FROM CuSn (Phosphor bronze) TO CuZn (Brass). PLATING CHANGED FROM MIN. 0.8µm GOLD PLATING TO MIN. 0.7µm PdNi+0.1µm GOLD FLASH AT CONTACT AREA.	27MAY2014	TJ	JK

  

POLZ.	L±0.5	BESTELL-NR.
1	2.54	△ -1
2	5.08	825 433 -2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1-
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2-
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5- 825 433 -0

  

LAGE DER VERRIEGELUNGSZAPFEN WECHSELN BEI UNGERADEN POLZAHLEN

△ MIN 0.7µm PdNi+0.1µm GOLD FLASH AT CONTACT AREA "F".  
MIN. 2.5µm TIN OVER 1.27µm NICKEL AT SOLDER AREA.

△ VARIANTE 825433-1 ERSETZT DURCH 826629-1

△ OBSOLETE PARTS

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT PIN	Cu Zn	△
HOUSING	PBT GV	GREEN
DESCRIPTION	MATERIAL	COLOR
		FINISH

  

DIMENSIONS: MASSENEHTEINheiten mm		DWN	10.05.84	MATERIAL	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		CHK	10.05.84	—	
±0.2 mm		APVD	10.05.84	OBERFLÄCHE/FARBE —	
0 PLC ± —		TE Connectivity			
1 PLC ± —					
2 PLC ± —					
3 PLC ± —					
4 PLC ± —		NAME			
ANGLES /WINKEL ± .		AMPMODU II PIN HEADER			
		PRODUCT SPEC PRODUKTSPEZ.		SIZE	CAGE CODE
		108-18012		DRAWING NO	RESTRICTED TO NUR FÜR
		APPLICATION SPEC VERARBEITUNGSSPEZ.		ZEICHNUNGS-NR.	—
		WEIGHT GEWICHT		A4 00779	—
		—		C-825433	—

  

CUSTOMER DRAWING /KUNDENZEICHNUNG		SCALE MASSSTAB	SHEET BLATT	OF VON	REV
		4:1	1	2	S

LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
VERWENDET FÜR _		—			—	—	—	
WAR NR. —		—			—	—	—	

  

POLZ.	L - 0.6	BESTELL-NR.
2	5.08	-2
3	7.62	5-825 433-3
4	10.16	5- -4
5	12.70	5- -5
6	15.24	5- -6
7	17.78	5- -7
8	20.32	5- -8
9	22.86	5- -9
10	25.40	6- -0
11	27.94	6- -1
12	30.48	6- -2
13	33.02	6- -3
14	35.56	6- -4
15	38.10	6- -5
16	40.64	6- -6
17	43.18	6- -7
18	45.72	6- -8
19	48.26	6- -9
20	50.80	7- -0
21	53.34	7- -1
22	55.88	7- -2
23	58.42	7- -3
24	60.96	7- -4
25	63.50	7- -5
26	66.04	7- -6
27	68.58	7- -7
28	71.12	7- -8
29	73.66	7- -9
30	76.20	8- -0
31	78.74	8- -1
32	81.28	8- -2
33	83.82	8- -3
34	86.36	8- -4
35	88.90	8- -5
36	91.44	8- -6
37	93.98	8- -7
38	96.52	8- -8
39	99.06	8- -9
40	101.60	9- -0
41	104.14	9- -1
42	106.68	9- -2
43	109.22	9- -3
44	111.76	9- -4
45	114.30	9- -5
46	116.84	9- -6
47	119.38	9- -7
48	121.92	9- -8
49	124.46	9- -9
50	127.00	5- -0

  

LAGE DER VERRIEGELUNGSZAPFEN WECHSELN BEI UNGERADEN POLZAHLEN

  

BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE
CAD-ORIGINAL		ZEICHNUNG NICHT ÄNDERN

  

ZEICHNUNG GÜLTIG AB		39./96..	
DWN A.HO 14.08.90		FINISH —	
CHK M.SCHAARSCHMIDT —		TE Connectivity	
APVD —			
PRODUCT SPEC —			
APPLICATION SPEC —		NAME AMPMODU II PIN HEADER	
SIZE A4	CAGE CODE 00779	DRAWING NO C-825433	RESTRICTED TO —
WEIGHT —		CUSTOMER DRAWING	
SCALE 4:1		SHEET 2 OF 2	REV S

  

DIMENSIONS:	
mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	
±0.2 mm	
0 PLC	± —
1 PLC	± —
2 PLC	± —
3 PLC	± —
4 PLC	± —
ANGLES	± —

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-825433-6](#)