


LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	CONTACT PIN MATERIAL AND PLATING CHANGE	22JUL2014	KJK	JK

NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄBLICH

POS. PER ROW	L±0.4	PART NUMBER	
-	-	-	
2	5.08	828 221 -2	OBSOLETE
3	7.62	-3	△
4	10.16	-4	
5	12.70	-5	OBSOLETE
6	15.24	-6	OBSOLETE
7	17.78	-7	
8	20.32	-8	OBSOLETE △
9	22.86	-9	OBSOLETE
10	25.40	-0	OBSOLETE
11	27.94	1-	-1
12	30.48	1-	-2 OBSOLETE
13	33.02	1-	-3 △
14	35.56	1-	-4 OBSOLETE
15	38.10	1-	-5 △
16	40.64	1-	-6 △
17	43.18	1-	-7 OBSOLETE
18	45.72	1-	-8 △
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1 △
22	55.88	2-	-2 △
23	58.42	2-	-3 △
24	60.96	2-	-4 △
25	63.50	2-	-5
26	66.04	2-	-6
27	68.58	2-	-7
28	71.12	2-	-8
29	73.66	2-	-9
30	76.20	3-	-0
31	78.74	3-	-1
32	81.28	3-	-2
33	83.82	3-	-3
34	86.36	3-	-4
35	88.90	3-	-5
36	91.44	3-	-6
37	93.98	3-	-7
38	96.52	3-	-8
39	99.06	3-	-9
40	101.60	4-	-0
41	104.14	4-	-1
42	106.68	4-	-2
43	109.22	4-	-3
44	111.76	4-	-4
45	114.30	4-	-5
46	116.84	4-	-6
47	119.38	4-	-7
48	121.92	4-	-8
49	124.46	4-	-9
50	127.00	5- 828 221 -0	OBSOLETE △



1 MATING SIDE: MIN. 0.7µm PdNi + MIN. 0.1µm GOLD FLASH BY AREA "F" OVER 1.27µm NICKEL
SOLDER SIDE : MIN. 2.5µm TIN OVER 1.27µm NICKEL

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT PIN	CuZn	△
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	COLOR FINISH

DIMENSIONS: mm	DWN R.NEBE 20.02.85	MATERIAL SEE TABLE	FINISH SEE TABLE
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M.SCHAARSCHMIDT 22.02.85	TE TE Connectivity	
0 PLC ±0.2 mm 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD -		
	PRODUCT SPEC 108-18012	NAME AMPMODU II PIN HEADER, DUAL ROW	
	APPLICATION SPEC -	SIZE A4	CAGE CODE 00779
	WEIGHT -	DRAWING NO C-828221	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
		REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[828221-7](#)