

C881545

G

F

E

D

C

B

A

8

7

6

5

4

3

2

1

DO NOT SCALE

DIMENSIONS IN mm.




METRIC

3rd ANGLE PROJECTION


ATENÇÃO

Este desenho esta sob o controle das especificações nos. 102-23 e 102-55. Toda e qualquer alteração, antes de ser processada, deverá ser comunicada aos clientes envolvidos, através dos procedimentos atuais.

Ver pasta "Notificação ao Cliente"



SECÇÃO A-A



SECÇÃO B-B

V2, COLOR GREEN (AMP A6484)

10 SIMILAR DO P/N 881545-2, PORÉM EM EMBALAGENS C/ 2.000 PEÇAS/SACO PLÁSTICO.

SIMILAR OF P/N 881545-2 BUT IN PACKAGES W/ 2.000 PARTS/ PLASTIC BAG.

11 MATERIAL HOUSING: TERMOPLÁSTICO COM 15% FIBRA DE VIDRO, V2, COR AMARELO (RAL 1016) CONTATO: BRONZE FOSFOROSO

MATERIAL HOUSING: THERMOPLASTIC 15% GLASS FIBER V2, COLOR YELLOW (RAL 1016) CONTACT: PHOSPHOROUS BRONZE.

12 MATERIAL HOUSING TERMOPLÁSTICO COM 15% FIBRA DE VIDRO, V2, COR VERDE (AMP A6484) CONTATO: BRONZE FOSFOROSO MATERIAL HOUSING THERMOPLASTIC 15% GLASS FIBER, V2, COLOR GREEN (AMP A6484) CONTACT: PHOSPHOROUS BRONZE.

13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

NOTAS:

NOTES:

1 MATERIAL: HOUSING: TERMOPLÁSTICO C/ FIBRA DE VIDRO V-0 COR: PRETO CONTATO: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER V-0 COLOR: BLACK CONTACT: PHOSPHOROUS BRONZE

2 MATERIAL: HOUSING: TERMOPLÁSTICO C/ FIBRA DE VIDRO HB COR: NATURAL CONTATO: BRONZE FOSFOROSO

MATERIAL: HOUSING: THERMOPLASTIC WITH GLASS FIBER HB COLOR: NATURAL CONTACT: PHOSPHOROUS BRONZE

3 0,38 µm. MIN. OURO NA ÁREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL 0,38 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

4 0,76 µm. MIN. OURO NA ÁREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL 0,76 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

5 1,27 µm. MIN. OURO NA ÁREA DE CONTATO, SOBRE BANHO 0,76 µm NIQUEL 1,27 µm. MIN. GOLD ON CONTACT AREA, 0,76 µm NIQUEL UNDERPLATING

6 ESTANHO SOBRE NIQUEL TIN OVER NICKEL

7 PONTO DE CONTATO V/ MEDIÇÃO DA CAMADA DE OURO CONTACT POINT FOR GOLD PLATING MEASUREMENT

8 ACEITA PINO QUADRADO 0,64 x 0,64 OU REDONDO Ø 0,64 ALLOW SQUARE PIN 0,64 x 0,64 OR ROUND Ø 0,64

9 MATERIAL: HOUSING: TERMOPLÁSTICO C/ 15% DE FIBRA DE VIDRO, V2, COR VERMELHO (PADRÃO DE COR: RAL 3000) CONTATO: BRONZE FOSFOROSO MATERIAL: HOUSING THERMOPLASTIC WITH 15% GLASS FIBER, V2, COLOR RED (STAND COLOR: RAL 3000) CONTACT: PHOSPHOROUS BRONZE.

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

OTHER TREATMENT

FINISH

MATERIAL

PART NUMBER

CUSTOMER DWG
for REFERENCE ONLY

THIS DRAWING IS UNPUBLISHED / RELEASED FOR PUBLICATION

TOLERANCES UNLESS OTHERWISE STATED
DEC. ±0.5
ANGLES ±1°

INS. DIA. RANGE

WIRE RANGE

SCALE

TE Connectivity

DESCRIPTION AMP SHUNT

LOW PROFILE CONNECTOR ASSY

REV. NO

DWG NO

REV. SHEET

A2

C 881545

K4 1 of 2


K4	REV. ECO 17-004195	HC	WLS	30MAY11	CHK	000	09-11-88
K3	REV. ECO11-023509	HC	WLS	02DEC11	CHK	000	09-11-88
K2	REVISED PER ECO-11-005139	RK	HMR	06APR11	CHK	000	09-11-88
ISS	REVISION RECORD	DR	CHK	DATE	APP	26/12/88	

C 881545

DO NOT SCALE
DIMENSIONS IN mm.

METRIC

3rd ANGLE PROJECTION



OBSOLETE 13	6	2	8
	6	2	7
	4	2	6
	3	2	881545-5
OBSOLETE 13	6	1	8
	6	1	7
	4	1	6
	3	1	5
OBSOLETE 13	6	1	4
	6	1	3
	4	1	2
	3	1	881545-1

OTHER TREATMENT	FINISH	MATERIAL	PART NUMBER
CUSTOMER DWG for REFERENCE ONLY		THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION	
SEE SHEET 1 OF 2		TOLERANCES UNLESS OTHERWISE STATED. DEC. ± 0.5 ANGLES $\pm 1^\circ$	INS. DIA. RANGE WIRE RANGE SCALE
		DR. <i>[Signature]</i> 11-09-88	ETE TE Connectivity
		CHK. <i>[Signature]</i> 08-11-88	
		DE. <i>[Signature]</i>	
ISS. REVISION RECORD	DR. CHK. DATE	APPR. <i>[Signature]</i> 29/10/88	DESCRIPTION AMP SHUNT LOW PROFILE CONNECTOR ASSY
A2			DWG NO. C 881545
REV. SHEET 2 OF 2			REV. SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-881545-2](#)