

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT 2020 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	20JAN2020	AFK	LS


FLATTENED WIDTH




D

d


w




EXPANDED TUBING PRODUCT



SPOOL



SPOOL I.D. 101 (4.0)




Product Size	2.4	3.2	4.8	6.4	9.5	12	18	25	38
"D" Minimum Supplied I.D.	2.4 (.094)	3.2 (.126)	4.8 (.189)	6.4 (.252)	9.5 (.374)	12.7 (.500)	19.1 (.752)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	0.8 (.031)	1.1 (.043)	1.6 (.063)	2.1 (.083)	3.2 (.126)	4.2 (.165)	6.4 (.252)	8.5 (.335)	19.1 (.752)
"w" Recovered Wall Thickness ±0.08 (.003)	0.51 (.020)	0.51 (.020)	0.58 (.023)	0.58 (.023)	0.61 (.024)	0.61 (.024)	0.61 (.024)	0.64 (.025)	0.64 (.025)
Minimum Sleeve Flattened Width	4.30 (.169)	5.82 (.229)	8.00 (.315)	10.65 (.419)	15.5 (.610)	20.4 (.803)	30.5 (1.201)	40.4 (1.591)	60.3 (2.374)

NOTES:  
1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm



MATERIAL  
CROSSLINKED POLYOLEFIN

FINISH  
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH  
-

DWN  
AFK

CHK  
-

APVD  
LS

PRODUCT SPEC  
RW-2519

APPLICATION SPEC  
-

WEIGHT  
VARIOUS


CUSTOMER DRAWING

09JAN2020

20JAN2020

VARIOUS

SCALE  
-

TE Connectivity

NAME  
D-CT  
OUTSIDE PRINTER SPOOL

SIZE  
A3

CAGE CODE  
0198G

DRAWING NO  
C-MCD170014

RESTRICTED TO  
-

SHEET  
1 OF 1

REV  
2

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8096-000](#)