



DRAWING NO. P0513

3RD ANGLE PROJECTION



REMOVE ALL SHARP EDGES AND BURRS



ANTI-DECOUPLING

DETAIL 'Z'

VIEW "Y"

1.55/0.89

90 DEG

NO.OF TEETH

A-THREAD



M

ANTI-DECOUPLING

R-THREAD

FROM FRONT OF CLAMP NUT
TO BEARING SURFACE

SHELL SIZE	B MAX	M +0 /-1.0	N +0 /-1.0	A-THREAD CLASS 2B	R-THREAD CLASS 2A
08	19.0	19.4	24.1	1/2-20UNF	5/8-24UNEF
10	22.3	20.0	24.8	5/8-24UNEF	7/8-20UNEF
12	25.4	20.6	25.4	3/4-20UNEF	1-20UNEF
14	28.7	21.0	26.1	7/8-20UNEF	1 1/16-18UNEF
16	31.7	21.7	26.6	1-20UNEF	1 3/16-18UNEF
18	33.5	22.1	26.9	1 1/16-18UNEF	1 5/16-18UNEF
20	36.5	22.8	27.4	1 3/16-18UNEF	1 7/16-18UNEF
22	39.8	23.5	28.4	1 5/16-18UNEF	1 9/16-18UNEF
24	42.9	24.0	29.2	1 7/16-18UNEF	1 3/4-18UNS
28	50.8	29.6	33.5	1 3/4-18UNS	2-18UNS

SCREW AND NUT SIZE
08-12 0.138-32UNC
14-28 0.164-32UNCCLINCH NUT,CAPTIVE
SILVER PLATED,SELF LOCKINGSCREW WITH WRENCHING RECESS
NAS7100 (NO CODE)
NASM14191 (CODE A)
NASM33781 (CODE A)

SHELL SIZE	E +0/-0.1	F +/-0.13	G +/-0.7	T +/-0.7	NO.OF TEETH	C +/-0.76	D MAX	J +/-0.4	L MAX
08	11.10	9.17	10.06	10.06	12	11.12	27.2	8.69	23.62
10	14.53	11.10	11.99	11.99	15	14.28	30.8	8.69	25.15
12	17.45	14.83	15.72	15.72	21	15.88	32.6	8.69	27.94
14	20.62	17.22	18.11	18.11	24	19.05	36.0	11.86	27.94
16	23.80	20.55	21.44	21.44	30	23.83	43.1	11.86	27.94
18	25.20	22.48	23.37	23.37	33	23.83	43.1	11.86	27.94
20	28.37	25.53	26.42	26.42	36	31.75	51.3	11.86	29.11
22	31.55	29.00	29.90	29.90	39	31.75	51.3	11.86	29.11
24	34.72	32.46	33.35	33.35	42	34.93	54.6	11.86	30.76
28	42.75	38.91	39.80	39.80	54	39.67	59.4	11.86	30.76

PART NO.SYSTEM

ESC77-E-14 A

SPEC NO. _____ WRENCHING RECESS
MATERIAL/FINISH _____
SHELL SIZE _____

2	DCR 395	11.4.01	A.D.P
1	FIRST ISSUE	16.12.92	D.C.P
ISSUE	DESCRIPTION	DATE	APPROVED

DRAWN	A.D.P.	16.12.92	MATERIAL/FINISH	UNLESS OTHERWISE SPECIFIED:- ALL DIMENSIONS IN MILLIMETRES TOLERANCE ON DIMENSIONS +/-0.1 TOLERANCE ON ANGLES +/-1 DEG	DO NOT SCALE THIS DRAWING THIS DRAWING IS COPYRIGHT,AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED,USED FOR MANUFACTURE OR OTHERWISE DISCLOSED,WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	POLAMCO LTD. WESTON LOCK LOWER BRISTOL ROAD BATH AVON	PART NO. ESC77-* **
CHECKED			D-STAINLESS STEEL PASSIVATED E-COUPLING NUT-ST STEEL PASSIVATED BODY-ALUMINIUM ELECTROLESS NICKEL	WEIGHT			ASSY USED ON
APPROVED 1				SCALE	N.T.S.		
APPROVED 2							
APPROVED 3							
PROJECT							
PART NO.	ESC77-* **						DRAWING NO. P0513

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ESC77-E10](#)