



PIDG

TE Part # 2-320576-3

TE Internal #: 2-320576-3

Mil-Spec: [M7928/1-67]

PIDG RING TONGUE TERMINALS

[View on TE.com >](#)

Terminals & Splices > Rings & Spades > PIDG RING TONGUE TERMINALS



Terminal & Splice Type: **Ring Tongue**

Wire Size: **12066 CMA**

Stud Size: **5/16, M8**

[All PIDG RING TONGUE TERMINALS \(428\)](#)

Features

Product Type Features

Shape Description	RING-041
Stud Size	5/16, M8
Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Wire/Cable Type	Regular Wire
Support Style	Insulation Restriction

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Weight per Piece	2.386 g
Stripe Color	Brown
Plating Material	Copper, Tin

Contact Features

Military Part Class	Class I
---------------------	---------



Terminal & Splice Type	Ring Tongue
Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	12066 CMA
Stud Diameter	7.92 mm[.312 in]
Tongue Thickness	1.07 mm[.042 in]
Overall Length	35.36 mm[1.392 in]
Wire Insulation Diameter	3.02 – 5.08 mm[.119 – .2 in]

Usage Conditions

Operating Temperature Range	105 °C[221 °F]
-----------------------------	----------------

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	Yes
----------------------	-----

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2017 (173)
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer







This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 <p>TE Part # 58423-1 DIE, RBY IS9252</p>	 <p>TE Part # 47808-6 DIE PIDG 69365 12-10</p>	 <p>TE Part # 2063030-1 SDE DIESET, RBY, UL</p>	 <p>TE Part # 59824-1 TETRA-CRIMP HT ASSY</p>
 <p>TE Part # 58433-3 PRO CR ASSY, RBY IS9252</p>	 <p>TE Part # 59239-4 HHHT PIDG 12-10</p>		

Also in the Series | PIDG

 <p>Crimp Terminal Housings (1)</p>	 <p>Crimp Wire Pins, Tabs &amp; Ferrules(41)</p>	 <p>Knife Disconnects(11)</p>	 <p>PCB Terminals(9)</p>
--	--	--	---



Portable Crimp Tools(1)



Quick Disconnects(53)



Rings & Spades(868)



Special Purpose Terminals (1)



Splices(48)

Customers Also Bought



TE Part #485937-000  
 S03-04-R-100



TE Part #324693  
 SPARE WIRE CAP,NAT, .048-.075 INS., MOIS




TE Part #423649-000  
 S03-05-R-100



TE Part #610002-000  
 D-300-12



TE Part #318821-000  
 SO96-3-01-100



TE Part #324694  
 SPARE WIRE CAP,RED .080-.115 INS., MOIS.



TE Part #066671-000  
 55A1832-14-MST3-9CS2275

Documents

Product Drawings

TERMINAL,PIDG R IR 10 5/16

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-320576-3\_S.2d\_dxf.zip



English

Customer View Model

ENG\_CVM\_CVM\_2-320576-3\_S.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-320576-3\_S.3d\_stp.zip

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

CSA Certificate

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M7928/1-67](#)