


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18JAN2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X



NOTES:

1. TECHNICAL DATA: SEE TABLE 1
- 2 STRIP AND RETAIN THE INSULATION
- 3 RECOMMEND TORQUE 0.4Nm
- 4 TE LABEL AREA.
- 5 -*: CABLE LENGHT. -0.5:0.5m, -1.0:1.0m, -1.5:1.5m...
- 6 INSERT MARK FOR MATING.
7. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

注意事项

1. 技术参数：见表 1
- 2 剥线并保留绝缘层；
- 3 推荐扭矩0.4Nm；
- 4 TE 标签位置；
- 5 -**线长：-0.5:0.5m，-1.0:1.0m，-1.5:1.5m
- 6 产品对插标示；
7. 产品必须符合ROHS与REACH.

TABLE 1

TECHNICAL DATA	T40513X0003-00X	T40513X0004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

WIRES: 0.25mm ² (24AWG)	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -**0:**.0m -**1:**.5m	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-FS-4CON-PUR-**5	4	T4051320004-00X
					RPC-M8-FS-3CON-PUR-**5	3	T4051320003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-FS-4CON-PVC-**5	4	T4051310004-00X
					RPC-M8-FS-3CON-PVC-**5	3	T4051310003-00X
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN Nick Pan 08DEC2015	TE Connectivity M8 CABLE ASSEMBLY SIGNLE ENDED FEMALE SIDE UNSHIELDED			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK Kobby Zhao 08DEC2015				
		0 PLC ±- 1 PLC ±0.35 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±- FINISH	APVD Xiang Xu 08DEC2015				
MATERIAL			PRODUCT SPEC 108-106140				
			APPLICATION SPEC -	SIZE A2	CAGE CODE -	DRAWING NO C-T40513X000X00X	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1	REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4051310004-002](#)