




Wire & Cable > Twisted Pair Cable



Twisted Pair Cable Type: **Spec 80**

Twisted Pair Cable Voltage Rating: **600 VAC**

Twisted Pair Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**

Twisted Pair Cable Conductor Material: **Tin-Coated Copper**

Wire Size: **10 AWG**

Features

Product Type Features

Twisted Pair Cable Type	Spec 80
-------------------------	---------

Electrical Characteristics

Twisted Pair Cable Voltage Rating	600 VAC
-----------------------------------	---------

Body Features

Twisted Pair Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Twisted Pair Cable Conductor Material	Tin-Coated Copper

Dimensions

Wire Size	10 AWG
-----------	--------

Usage Conditions

Operating Temperature Range	-65 – 150 °C
-----------------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 0662-207-0882  
CONT SOC ASSY

Customers Also Bought



TE Part #060263-000  
TXR40AB90-2410AI



TE Part #YDTS26W25-19PCC001  
D38999: Straight Plug, 25-19 Insert



TE Part #1738025-1  
Pin Contact, Size 15



TE Part #1738149-1  
Insert Asy, Socket, GPRBE22SA





TE Part #265930-000  
81044/9-4-5



TE Part #761349-000  
9530J1424-9X



TE Part #CLP-100  
LINEAR POT, IP65, 100MM RANGE



TE Part #1-1617118-3  
J1MACD-12XLS = M39016/23-034L



TE Part #1-1617168-1  
JMSCT-26XMS = M28776/3-046M



TE Part #C92466-000  
TX40AB00-2216H

Documents

Product Drawings

82A1121-10-6/9-9

English

Datasheets & Catalog Pages

1654025\_Sec9\_SPEC80

English

Raychem Wire and Cable Quick Reference Guide

English

Product Specifications

Product Specification

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[82A1121-10-6/9-9](#)