



Terminals & Splices > Splices



Splice Product Type: **Sealing Sleeve**

Sealable: **Yes**

Splice Type: **Sealing Sleeve**

Serrated: **No**

Number of Serrations: **0**

Features

Product Type Features

Splice Product Type	Sealing Sleeve
Sealable	Yes
Splice Type	Sealing Sleeve
Serrated	No
Splice Wire/Cable Type	Insulated Wire
Insulated	Yes
Support Style	Non-Insulation Support

Configuration Features

Number of Serrations	0
----------------------	---

Dimensions

Splice Overall Length	29.2 mm[1.15 in]
-----------------------	------------------

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards



Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Splice Packaging Method	Bag/Box
-------------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 992008-000

[AD-1377-CRIMP-TOOL-3-CVTY](#)

Customers Also Bought



TE Part #53052  
PIDG RING TONGUE TERMINALS

TE Part #9-1879649-7  
H4P 115K 0.5% 100PPM

TE Part #103976-3  
5X4 MTE RCPT SR PLAIN .100CL

TE Part #3-1617784-0  
FCA-210-1015L=M83536/10-015L

TE Part #929441-000  
55A1841-22-0/2/5/9-3

TE Part #ABC26C-0000A  
PLUG ASSY

TE Part #C60253N001  
D-200-84CS2901

TE Part #CN5421-000  
S200-5-00-TC

TE Part #YDL60R-14-4S8C0120  
RECP ASSY

TE Part #A70291-000  
MTCP-122-20P2-001

Documents

Product Drawings  
D-436-0098CS391

English

Datasheets & Catalog Pages  
1654025\_Sec8\_D-436

English

Harness Repair Products Quick Reference Guide  
English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D-436-0098CS391](#)