

D

C

B

A

D

C

B

A




TABLE 1

TECHNICAL DATA	T40521X4003-00X	T40521X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

- NOTES:
1. TECHNICAL DATA: SEE TABLE 1

2. RECOMMEND TORQUE 0.4Nm

3. TE LABLE AREA.

4. -*: CABLE LENGHT. -0.5:0.5m, -1.0:1.0m, -1.5:1.5m...

5. INSERT MARK FOR MATING.

6. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

- 注意事项
1. 技术参数: 见表1

2. 推荐扭矩0.4Nm;


3. TE 标签位置;

4. -*线长: -0.5:0.5m, -1.0:1.0m, -1.5:1.5m

5. 产品对插标示;

6. 产品必须符合ROHS与REACH.

		TE LABLE	10
		CABLE	9
	COPPER ALLOY	NUT	8
	RUBBER	O-RING	7
	PA66	HOUSING	6
	COPPER ALLOY	CONTACT	5
	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	-001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MS-***-M8-4FR-PUR	4	4	T4052124004-00X
					RPC-M8-3MS-***-M8-3FR-PUR	4	3	T4052124003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4MS-***-M8-4FR-PVC	4	4	T4052114004-00X
					RPC-M8-3MS-***-M8-3FR-PVC	4	3	T4052114003-00X
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE		POS.	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 25FEB2016 Nick Pan CHK 25FEB2016 Kobby Zhao APVD 25FEB2016 Xiang Xu		TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		M8 CABLE ASSEMBLY UNSHIELDED TYP DOUBLE ENDED		
		0 PLC ± 1 PLC ±0.50 2 PLC ±0.35 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-106140		-		
MATERIAL TBD		FINISH -		APPLICATION SPEC -		SIZE A2		CAGE CODE C-T40521X400X00X
				RESTRICTED TO -				
CUSTOMER DRAWING					SCALE 1:1		SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052114003-005](#)