






TABLE 1

TECHNICAL DATA	T40522X3003-00X	T40522X3004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

		TE LABLE	10
		CABLE	9
	COPPER ALLOY	NUT	8
	RUBBER	O-RING	7
	PA66	HOUSING	6
	COPPER ALLOY	CONTACT	5
	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	-001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-***-M8-4FS-PUR	4	4	T4052223004-00X
					RPC-M8-3MR-***-M8-3FS-PUR	4	3	T4052223003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4MR-***-M8-4FS-PVC	4	4	T4052213004-00X
					RPC-M8-3MR-***-M8-3FS-PVC	4	3	T4052213003-00X
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE		POS.	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				TE Connectivity				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		M8 CABLE ASSEMBLY UNSHIELDED TYP DOUBLE ENDED				
mm		0 PLC ± 1 PLC ±0.5 2 PLC ±0.35 3 PLC ± 4 PLC ±		-				
		ANGLES ±		-				
MATERIAL		FINISH		RESTRICTED TO				
TBD		-		-				
material_2		finish_spec_2		-				
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1		REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052213004-003](#)