





TECHNICAL DATA	T40522X3003-00X	T40522X3004-00
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

		TE LABLE	10
		CABLE	9
	COPPER ALLOY	NUT	8
	RUBBER	O-RING	7
	PA66	HOUSING	6
	COPPER ALLOY	CONTACT	5
	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPTON	ITEM



WIRES: 0.25mm ² (24AWG)	-001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-**-M8-4FS-PUR	4	4	T4052223004-00X
					RPC-M8-3MR-**-M8-3FS-PUR	4	3	T4052223003-00X
					RPC-M8-4MR-**-M8-4FS-PVC	4	4	T4052213004-00X
					RPC-M8-3MR-**-M8-3FS-PVC	4	3	T4052213003-00X
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE		POS.	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.					TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME			
		0 PLC ±- 1 PLC ±0.5 2 PLC ±0.35 3 PLC ± 4 PLC ± ANGLES ±- FINISH			DWG Nick Pan 25FEB2016 CHK Kobby Zhao 25FEB2016 APVD Xiang Xu 25FEB2016			
MATERIAL TBD		-			PRODUCT SPEC 108-106140			
material 2		finish spec 2			APPLICATION SPEC -			
					WEIGHT -			
CUSTOMER DRAWING					SIZE A2		CAGE CODE -	DRAWING NO C-T40522X300X00X
					RESTRICTED TO -			
					SCALE 1:1		SHEET 1 of 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052223004-001](#)