



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Cannot be Certified**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content




Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 321066
TERMINAL,SOLIS FLAG R 1/0 3/8




TE Part # 322215
TERMINAL,SOLIS FLAG R 1/0 1/4



TE Part # 321580
TERMINAL,SOLIS FLAG R 1/0 5/16



TE Part # 1490749-1
HYP10 8-4/0AWG MANUAL TOOL



TE Part # 1490746-1
HYP10 LIGHT DUTY 14T HEAD

Customers Also Bought



TE Part #YDTS24F13-98JNV001
RECP ASSY



TE Part #YDTS26F13-98JNV001
PLUG ASSY




TE Part #YDTS26F15-05JNV001
PLUG ASSY



TE Part #1-87348-4
14 MODII HDR SRST UNSHRD .100






TE Part #1752681-1
HYP10 SOLIS FLAG 1/0-4/0AWG
INDENTER




TE Part #2150283-2
OCEAN_2.0_Applicator-S-080F130F




TE Part #2150551-1
OCEAN_2.0_Applicator-E-110F120O



TE Part #55850-1
16-14 PRE-INSUL SEALED TERM R



TE Part #55857-1
12-10 PRE-INSUL SEALED TERM R



TE Part #696423-9
TERMINAL,PIDG PVF2 R 16-14 3/8

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1752680-4](#)