

AMP Signal Double Lock

TE Internal #: 2108641-1

AMP Signal Double Lock, Housing, Receptacle, Wire-to-Board, 11 Position, 2.5mm [.098in] Centerline, Crimp, 1 Row, Natural Housing Color

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > STD Temp Signal Double Lock Header



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **11**

Centerline (Pitch): **2.5 mm [ .098 in ]**

All STD Temp Signal Double Lock Header (6)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	11
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

--	--



Connector Profile	Standard
-------------------	----------

Contact Features

Contact Layout	Inline
Contact Retention Within Housing	With
Contact Type	Tab

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

PCB Mount Alignment Type	Boss
Strain Relief	Without
Contact Retention Type Within Housing	Double Lock Plate
PCB Mount Alignment	With
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Nylon 6/6 GF
Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	Natural

Dimensions

Connector Length	30 mm[1.181 in]
Connector Height	8.2 mm[.322 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Bag

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1376478-2  
2.5 SMC HDR 2POS WHITE (LP)



TE Part # CAT-SI261-H342  
STD Temp Signal Double Lock Header




TE Part # 917731-1  
2.5 S.D.L P.HDR ASY 11P H/PRO.



TE Part # 1376478-3  
2.5MM SIGNAL MATE CONN HEADER



TE Part # 917789-1  
2.5 S.D.L POST HDR ASY 11P STD



TE Part # 1376478-4  
2.5MM SIGNAL MATE CONN HEADER




Also in the Series | AMP Signal Double Lock

Connector Contacts(9)	Insertion & Extraction Tools(1)	PCB Connector Seals(1)	PCB Latches, Locks & Retainers(17)
Rectangular Caps & Covers(1)	Rectangular Connector Housings(23)	Rectangular Connector Locking(2)	Rectangular Connector Seals(10)
Rectangular Power Connectors(3)	Standard Rectangular Connectors(1)	Wire-to-Board Connector Assemblies & Housings(74)	Wire-to-Board Connector Contacts(6)
Wire-to-Board Headers & Receptacles (157)			

Customers Also Bought

TE Part #316094-1 2.5 SIGNAL D/LOCK CAP HSG 10P	TE Part #36189 BUDG R 22-16 COMM 22-18 MIL 4	TE Part #1625854-4 1206 PROBE PAD	TE Part #1825910-7 FSM4JAH=6MM TACT SWITCH, HIGH TEMP



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2108641-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2108641-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2108641-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2108641-1](#)