

2226910-2 ✓ ACTIVE

O.C.H. Micro Circular Connectors

TE Internal #: 2226910-2

O.C.H. Micro Circular Connectors, Standard Circular Connectors,  
Wire-to-Wire, 6 Position, Sealable, Wire & Cable, 5A Contact  
Current Rating (Max)

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **6**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **5 A**

### Features

#### Product Type Features

Accessory Color	Black
Prewired	No
Product Type	Connector Kit
Assembly Type	Electrical Connector
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Plug

#### Configuration Features

Keying & Polarized Position Locations	Normal
Factory Installed Backshell	No
Keying	Triple Key
Number of Positions	6
Number of Power Positions	0
Number of Signal Positions	6
Contacts Preloaded	No



### Body Features

Shield Rating	100 - 10000 MHz
Environmental Protection Type	Elastomer Sealed
Entry Style	Rear Insertion
Peripheral Seal Material	Fluorosilicone Elastomer
Positive Stop Ferrule	Without
Environmental Protection	With
Weight	2.62 g
O-Ring Material	Fluorosilicone
Fluid Type	None
Feedthrough Type	No
Shell Plating Material	Black Zinc Nickel
Shell Base Material	Aluminum 6061-T6
Circular Connector Insulation Material Type	LCP (Liquid Crystal Polymer)
Hermetically Sealed	No

### Contact Features

Contact Current Rating (Max)	5 A
Reverse Gender	No
Circular Connector Contact Type	Pin

### Mechanical Attachment

Mating Alignment	With
Mating Retention Type	Push-Pull Self-Locking
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Panel Mount Feature Type	Flanged
Polarization Code	Normal
Mating Alignment Type	Keyed
Mating Retention	With

### Housing Features

Circular Connector Shell Size	6
Alignment Keyed	Insert Clocking

### Dimensions



Accepts Wire Insulation Diameter Range	1.32 mm[.03 – .054 in]
Assembly Length	25.2 mm[.99 in]
Wire Size	22 – 24 AWG

### Usage Conditions

IP Dust Sealing Level	5
Fluid Resistance	Immersible
Operating Temperature Range	-20 – 80 °C

### Operation/Application

Durability Rating	2000 Cycles
Circuit Application	Signal
Shielded	Yes

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	1
--------------------	---

### Other

Position Locations Omitted	All
Field Serviceable	No

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2226920-1  
NETT WARRIOR RECEPTACLE ASSEMBLY

### Also in the Series | O.C.H. Micro Circular Connectors



Connector Contacts(2)




Crimp Wire Pins, Tabs & Ferrules(1)



Standard Circular Connectors(6)

### Customers Also Bought



TE Part #661269-000  
TXR21AB00-1605AI




TE Part #1617807-5  
FC-335-SY8= RELAY, 3PST



TE Part #642427-000  
242A312-12-03-0



TE Part #1617147-5  
JMGAP-26P = M39016/17-030P



## Documents

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2226910-2\\_M.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2226910-2\\_M.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2226910-2\\_M.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[O.C.H. Micro Circular Connectors](#)

English

### Product Specifications

[Product Specification](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2226910-2](#)