





TABLE 1

TECHNICAL DATA	T40622X4003-00X	T40622X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

-	-	TE LABLE	14
	STEEL	WAVE WASHER	13
	STEEL	SPRING	12
	BRASS	SHIELDING	11
-	-	CABLE	10
-	COPPER ALLOY	COUPLING NUT	9
	RUBBER	O-RING	8
BALCK COLOR	PA66	HOUSING	7
GOLD FLASH	COPPER ALLOY	CONTACT	6
	COPPER ALOY	SHIELDING	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm²
(24AWG)

STANDARD:
-001:0.5M
-002:1.0M
-003:1.5M
-004:3.0M
-005:5.0M
-006:7.0M
-007:10.0M
CUSTOMIZATION:
-XX0:XX.0 M
-XX5:XX.5 M
-99X: 0.X M

FIXED:
-25°C~80°C
FLXIBLE:
-10°C~80°C

FIXED:
-10°C~80°C
FLXIBLE:
-5°C~80°C

GRAY

BLACK

PUR
(UL)

PVC
(UL)

RPC-M8-4MR-**SH-M8-4FR-PUR

RPC-M8-3MR-**SH-M8-3FR-PUR

RPC-M8-4MR-**SH-M8-4FR-PVC

RPC-M8-3MR-**SH-M8-3FR-PVC

4

3

4

3

T4062224004-00X

T4062224003-00X

T4062214004-00X

T4062214003-00X

CABLE CHARACTERISTIC

LENGTH "L"

RECOMMEND OPERATION TEMPERATURE FOR CABLE

JACKET COLOR

JACKET MATERIAL

TYPE

POS.

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.50
2 PLC ±0.35
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

TBD

DWN

24FEB2016

CHK

24FEB2016

APVD

24FEB2016

PRODUCT SPEC

108-106140

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

M8 CABLE ASSEMBLY SHIELDED TYPE DOUBLE ENDED

SIZE

A2

CAGE CODE

-

DRAWING NO

©T40622X400X00X

RESTRICTED TO

-

SCALE

1:1

SHEET

1

OF

1

REV

B

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4062214003-004](#)