




AMP

TE Internal #: 58564-2

Portable Crimp Tools, Commercial Crimp Tooling, Operator Releasable & Adjustable, Removable/Interchangeable, TE Product Specification (114-)

[View on TE.com >](#)

Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Operator Releasable & Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 175156-2 U/P REC CONT L/P	 TE Part # 175153-1 UNIV POWER TAB CONT L/P	 TE Part # 175149-1 UNIVERSAL POWER CONN TAB	 TE Part # 175151-1 AMP UNIVERSAL POWER REC CONT.
 TE Part # 175152-1 UNIVERSAL POWER REC	 TE Part # 175152-2 AMP UNIVE. POWER CONN REC CONT	 TE Part # 175149-2 AMP UNIVE. POWER CONN TAB CONT	 TE Part # 175150-2 AMP UNIVE. POWER CONN TAB CONT
 TE Part # 175151-2 AMP UNIVE. POWER CONN REC CONT	 TE Part # 175153-2 U/P TAB CONT L/P	 TE Part # 175155-2 U/P REC CONT L/P	 TE Part # 175156-1 UNIV POWER REC CONT L/P



			
TE Part # 175154-2 U/P TAB CONT L/P	TE Part # 175155-1 UNIV POWER REC CONT L/P	TE Part # 175150-1 UNIVERSAL POWER CONN TAB	TE Part # 175151-5 AMP UNIVERSAL POWER CONN.REC C
			
TE Part # 175154-1 UNIV POWER TAB CONT L/P	TE Part # 175149-3 AMP UNIVERSAL POWER CONN.TAB C	TE Part # 175151-4 UNIVESAL POWER REC CONT #26-22	TE Part # 175152-3 UNIV POWER REC CONT

Customers Also Bought

			
TE Part #4-1879352-2 RR02 5% 16R AMMO	TE Part #3-2176330-5 CRGP 2010 6K8 1%	TE Part #2329358-4 PB OFF/ON HC GRE M1 TERM IP68 500MM L	TE Part #1879352-6 RR02 5% R51 AMMO
			
TE Part #1879354-6 RR03 5% R51 AMMO	TE Part #4-745130-3 SHLDING FERRULE,PLTD,BULK PKG	TE Part #176153-3 EIS POST HDR ASSY H 3P GOLD	TE Part #2820883008 44A0111-28-8
			
TE Part #3827673001 44A1131-20-0/2/9-0	TE Part #CD00193001 RAY-90-6.0(100)CK1100		

Documents



Datasheets & Catalog Pages

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[58564-2](#)