




Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-), UL/CSA**
TE Certification: **Upon Request for Fee**
Power Technology Type: **Battery, Electric, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-), UL/CSA
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability










Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 4-521098-2 ULTRA-FAST 250 ASSEMBLY 12-10 AWG TPBR</p>	 <p>TE Part # 4-521097-2 ULTRA-FAST 250 ASY TAB 12-10 AWG TPBR</p>	 <p>TE Part # 4-520448-2 ULTRAFAST 250 ASSY REC 12-10 TPBR LP</p>	 <p>TE Part # 4-520447-2 ULTRA-FAST 250 ASY REC 12-10 AWG TPBR</p>
--	--	--	---

Customers Also Bought

 <p>TE Part #3-520151-2 ULTRAFAST 187 ASSY REC 16-14 TPBR LP</p>	 <p>TE Part #3-640428-9 09P MTA156 CONN ASSY 22AWG RED</p>	 <p>TE Part #1-480720-0 02P CMNL PLUG HSG W/LOK NATL</p>	 <p>TE Part #2-747580-3 SHLDING FERRULE,PLTD TIN,BULK</p>
 <p>TE Part #2-320568-1 TERMINAL,PIDG R 12-10 8</p>	 <p>TE Part #1-456401-6 CRIMPER, WIRE .042 "F"</p>	 <p>TE Part #201311-3 FEMALE BLOCK MIN. RECT.</p>	 <p>TE Part #YD369-G99-NP400000 369 9 WAY INLINE 90 PCB REC, GOLD, PIN</p>



TE Part #3-1478996-6
Cable Boot Black RG55, 58, 141

Documents

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[58630-2](#)