


COIL: @ 25° C
 RESISTANCE 675 OHMS ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.5 VDC
 MUST RELEASE 1.47 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE TIME 5 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 3 AMPS
RESISTIVE 28 VDC 100,000 OPERATIONS

DR. R.B. 8/25/98 CK. 8/25/98

COMMUNICATIONS
 INSTRUMENTS, INC.

FW1209G00

CUST. C.I.I. STD.
 CUST. NO. _____

TYPE "FW" RELAY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1617020-3](#)