

COIL: @ +25 °C

RESISTANCE 700 OHMS \pm 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 15.0 VDC

MUST RELEASE 8.0 VDC MAX 1.5 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 100 g's 6 ± 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C


NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE
OF -48 VDC WITH BIFILAR COIL

OPERATE & RELEASE 5 MS MAX.

CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET

BLUE BEAD



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/14/95 CK. *[Signature]*

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M39016/22-009M

TYPE "HMB" RELAY

HMB1201K01M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1617038-1](#)