

REV. 2 9/12/97

COIL: @ 25°C

RESISTANCE 1560 OHMS \pm 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.2 VDC

MUST RELEASE 1.37 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's


SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX; RELEASE TIME 4.0 MS MAX; CONTACT BOUNCE 15 MS MAX

TERMINAL FINISH SOLDER DIPPED, BUILT IN
ACCORDANCE WITH MIL-R-39016

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 4/4/95 CK. 10/12/97

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.

CUST. NO.

TYPE MGAD RELAY

MGACD-26

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1617154-1](#)