

REV. 0
DCO 143043


COIL: @ 25°C
 RESISTANCE $1560 \text{ OHMS} \pm 10\%$
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.2 VDC
 MUST RELEASE $8.0 \text{ VDC MAX.}, 1.37 \text{ VDC MIN.}$

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 $^\circ\text{C}$ TO $+125$ $^\circ\text{C}$

NOTES: OPERATE TIME 2.0 MS MAX.
 RELEASE TIME 1.5 MS MAX.
 CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
 $28 \text{ VDC RESISTIVE } 100,000 \text{ OPERATIONS}$

DR. B.D. 6/27/01 CK. 6/27/01

CII Technologies
 advanced control electronic solutions

CUST. CII
 CUST. NO. COTS STD. REV.

TYPE
 "PRMA" RELAY

PRMAP-26X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1617108-5](#)