


COIL: @ 25°C
 RESISTANCE 390 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 7.0 VDC
 MUST RELEASE 4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX
 RELEASE TIME 4.0 MS MAX
 CONTACT BOUNCE TIME 15 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 1 AMP 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 1/16/98 CK 10/20/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C. I. I. STD.

CUST. NO. REV.

SMGAD RELAY

SMGAD-12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1617352-0](#)