




Bestückungsplan / contact layout

■ bestückt / assemble



Leiterplatten-Lochbild / PCB drillhole pattern



Elastische Einpresszone mit Übergabesteckzone /
compliant pressfit zone with mating transfer zone

Isolierwerkstoff / housing material : PBT GF30

Bauart 7 / type 7

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles

Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062/Nr.6

diameter of drilled hole see drawing 164062/Na.6

1) $\phi 1,0 \pm 0,09$ Durchmesser des metallisierten Loches

$\phi 1,0 \pm 0,06$ Diameter of finished plated-through hole

$\phi 1,15 \pm 0,025$ Bohrungsdurchmesser des Loches

$\phi 1,15 \pm 0,025$ Diameter of drilled hole

ohne Flansch

without flange

Consider protection memo from DIN 34

Information:	Tolerances	 All Dimensions in mm	Scale 2:1
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	Designation Federleiste C/2, 48 EE Fem. Con. C/2, 48 Pressfit	
Index	Date	ERNI www.ERNI.com	254894
		H:00060851.SZA	STVC/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[254894](#)