





D

C


B

A



RECOMMENDED HOLE LAYOUT

- 1
- THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 2
- POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3
- POSTS: .000030 GOLD IN CONTACT AREA .000100-.000200 MATTE TIN LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 4
- POSTS: .000030 GOLD IN CONTACT AREA .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION X-X

REVISIONS										
P	LTR	DESCRIPTION					DATE	DWN	APVD	
	N5	REVISED	PER	ECN-24-247102			23JAN2024	RK	MF	
5	OBSOLETE	4		3.490	.190	3.800	3.500	35	72	8-103167-3
5	OBSOLETE	4		3.390	.190	3.700	3.400	34	70	8-103167-2
		4		3.290	.190	3.600	3.300	33	68	8-103167-1
5	OBSOLETE	4		3.190	.190	3.500	3.200	32	66	8-103167-0
5	OBSOLETE	4		3.090	.190	3.400	3.100	31	64	7-103167-9
5	OBSOLETE	4		2.990	.190	3.300	3.000	30	62	7-103167-8
		4		2.890	.190	3.200	2.900	29	60	7-103167-7
5	OBSOLETE	4		2.790	.190	3.100	2.800	28	58	7-103167-6
5	OBSOLETE	4		2.690	.190	3.000	2.700	27	56	7-103167-5
5	OBSOLETE	4		2.590	.190	2.900	2.600	26	54	7-103167-4
5	OBSOLETE	4		2.490	.190	2.800	2.500	25	52	7-103167-3
5	OBSOLETE	4		2.390	.190	2.700	2.400	24	50	7-103167-2
5	OBSOLETE	4		2.290	.190	2.600	2.300	23	48	7-103167-1
5	OBSOLETE	4		2.190	.190	2.500	2.200	22	46	7-103167-0
5	OBSOLETE	4		2.090	.190	2.400	2.100	21	44	6-103167-9
5	OBSOLETE	4		1.990	.190	2.300	2.000	20	42	6-103167-8
		4		1.890	.190	2.200	1.900	19	40	6-103167-7
5	OBSOLETE	4		1.790	.190	2.100	1.800	18	38	6-103167-6
5	OBSOLETE	4		1.690	.190	2.000	1.700	17	36	6-103167-5
		4		1.590	.190	1.900	1.600	16	34	6-103167-4
5	OBSOLETE	4		1.490	.190	1.800	1.500	15	32	6-103167-3
		4		1.390	.190	1.700	1.400	14	30	6-103167-2
5	OBSOLETE	4		1.290	.190	1.600	1.300	13	28	6-103167-1
		4		1.190	.190	1.500	1.200	12	26	6-103167-0
		4		1.090	.190	1.400	1.100	11	24	5-103167-9
		4		.990	.190	1.300	1.000	10	22	5-103167-8
		4		.890	.190	1.200	.900	9	20	5-103167-7
		4		—	.490	1.100	.800	8	18	5-103167-6
		4		—	.390	1.000	.700	7	16	5-103167-5
		4		—	.390	.900	.600	6	14	5-103167-4
		4		—	.290	.800	.500	5	12	5-103167-3
		4		—	.290	.700	.400	4	10	5-103167-2
5	OBSOLETE	4		—	.190	.600	.300	3	8	5-103167-1
5	OBSOLETE	3		3.490	.190	3.800	3.500	35	72	3-103167-3
5	OBSOLETE	3		3.390	.190	3.700	3.400	34	70	3-103167-2
		3		3.290	.190	3.600	3.300	33	68	3-103167-1
5	OBSOLETE	3		3.190	.190	3.500	3.200	32	66	3-103167-0
5	OBSOLETE	3		3.090	.190	3.400	3.100	31	64	2-103167-9
5	OBSOLETE	3		2.990	.190	3.300	3.000	30	62	2-103167-8
		3		2.890	.190	3.200	2.900	29	60	2-103167-7
5	OBSOLETE	3		2.790	.190	3.100	2.800	28	58	2-103167-6
5	OBSOLETE	3		2.690	.190	3.000	2.700	27	56	2-103167-5
5	OBSOLETE	3		2.590	.190	2.900	2.600	26	54	2-103167-4
5	OBSOLETE	3		2.490	.190	2.800	2.500	25	52	2-103167-3
		3		2.390	.190	2.700	2.400	24	50	2-103167-2
5	OBSOLETE	3		2.290	.190	2.600	2.300	23	48	2-103167-1
5	OBSOLETE	3		2.190	.190	2.500	2.200	22	46	2-103167-0
5	OBSOLETE	3		2.090	.190	2.400	2.100	21	44	1-103167-9
5	OBSOLETE	3		1.990	.190	2.300	2.000	20	42	1-103167-8
		3		1.890	.190	2.200	1.900	19	40	1-103167-7
5	OBSOLETE	3		1.790	.190	2.100	1.800	18	38	1-103167-6
5	OBSOLETE	3		1.690	.190	2.000	1.700	17	36	1-103167-5
		3		1.590	.190	1.900	1.600	16	34	1-103167-4
		3		1.490	.190	1.800	1.500	15	32	1-103167-3
		3		1.390	.190	1.700	1.400	14	30	1-103167-2
5	OBSOLETE	3		1.290	.190	1.600	1.300	13	28	1-103167-1
		3		1.190	.190	1.500	1.200	12	26	1-103167-0
		3		1.090	.190	1.400	1.100	11	24	103167-9
		3		.990	.190	1.300	1.000	10	22	103167-8
		3		.890	.190	1.200	.900	9	20	103167-7
OBSOLETE		3		—	.490	1.100	.800	8	18	103167-6
		3		—	.390	1.000	.700	7	16	103167-5
		3		—	.390	.900	.600	6	14	103167-4
		3		—	.290	.800	.500	5	12	103167-3
		3		—	.290	.700	.400	4	10	103167-2
		3		—	.190	.600	.300	3	8	103167-1
PLATING		E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

0. PLC
1. PLC
2. PLC
3. PLC
4. PLC
ANGLES

± -
± -
± -
± .005
± -
± -

MATERIAL

HOUSING: FLAME RESISTANT THERMOPLASTIC COLOR: BLACK POSTPHOS BRONZE

FINISH

SEE TABLE

WEIGHT

—

CUSTOMER DRAWING

DWN
H. MOLL
27JUL87

CHK
R. FEIDT
28JUL87

APVD
R. FLICKER
29JUL87

NAME

HDR ASSY, MOD II, SHROUDED, 4 SIDES, DR, .100X.100 RIGHT ANGLE, W/ .025 SQ POSTS

SIZE

A1

CAGE CODE

00779

DRAWING NO

103167

RESTRICTED TO

—

TE Connectivity

SCALE 4:1

SHEET 1 OF 1

REV N5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-103167-7](#)